







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B4	ECR-11-007201	06APR2011	SPB	JM
			B5	ECR-14-015672	21OCT2014	QP	XR

CODINGS
SCALE 5:1

SECTION A-A



2:1

NOTES:

- 1 SELECTIVE PLATING IN THIS AREA >0.8 microns GOLD OVER >2.0 microns NICKEL
- 2 GENERAL TOLERANCE UNLESS OTHERWISE STATED $\pm 0.1\text{mm}$
3. PACKAGING - LOOSE PIECE
- 4 MOULD IMPRESSION NUMBER
- 5 ASSEMBLY MANUFACTURING DATE CODE (DD.MM.YY)

3-1703884-2	C	2	SHORTING CLIP	Cu ALLOY		
		1	SCR HOUSING	10% G.F. PBT	ORANGE	2007
3-1703884-1	C	2	SHORTING CLIP	Cu ALLOY		
		1	SCR HOUSING	10% G.F. PBT	BLUE	5012
2-1703884-2	B	2	SHORTING CLIP	Cu ALLOY		
		1	SCR HOUSING	10% G.F. PBT	GREY	7037
2-1703884-1	B	2	SHORTING CLIP	Cu ALLOY		
		1	SCR HOUSING	10% G.F. PBT	GREEN	6032
1-1703884-6	A	2	SHORTING CLIP	Cu ALLOY		
		1	SCR HOUSING	10% G.F. PBT	GREEN	6032
1-1703884-5	A	2	SHORTING CLIP	Cu ALLOY		
		1	SCR HOUSING	10% G.F. PBT	PURPLE	4006
1-1703884-4	A	2	SHORTING CLIP	Cu ALLOY		
		1	SCR HOUSING	10% G.F. PBT	RED	3000
1-1703884-3	A	2	SHORTING CLIP	Cu ALLOY		
		1	SCR HOUSING	10% G.F. PBT	YELLOW	1016
1-1703884-2	A	2	SHORTING CLIP	Cu ALLOY		
		1	SCR HOUSING	10% G.F. PBT	BLUE	5012
1-1703884-1	A	2	SHORTING CLIP	Cu ALLOY		
		1	SCR HOUSING	10% G.F. PBT	BLACK	9012
ASSEMBLY No.	CODE	POSN	DESCRIPTION	MATERIAL	COLOUR	RAL NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
Linear : ± 0.1

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

DWN
J.Marsh
15 JUN 07

CHK
B.Baker
15 JUN 07

APVD

PRODUCT SPEC
108-3644

APPLICATION SPEC

WEIGHT
0.5 g

NAME
2 POS, SHORT CIRC SPR, HOUSING ASSY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

MATERIAL

SEE ABOVE

CUSTOMER DRAWING

SCALE 10:1

SHEET 1 OF 1

REV B5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1703884-1](#)