


LOC	DIST	REVISIONS			
		P	LTR	DATE	APVD
DF	A5	B		REVISED PER ECO-08-029679	22DEC2008

- THIS CONNECTOR ACCEPTS TYCO ELECTRONICS QUARDAX SOCKET ASSEMBLY, PART# 1445692-3 (CONTACTS NOT INCLUDED).
- OPERATING TEMPERATURE RANGE: -65°C TO 125°C (-85°F TO 257°F).
- QUADRAX PIN CONTACT, 1445692-3, SOLD SEPARATELY.
- THE CONNECTOR QUALIFICATION WAS COMPLETED PER TYCO ELECTRONICS 108-2199. THE QUADRAX CONTACTS ARE QUALIFIED PER TYCO ELECTRONICS 108-2131. THE REFERENCE TEST REPORTS ARE TYCO ELECTRONICS 501-660 FOR THE CONNECTOR AND 501-574 FOR THE CONTACTS WHICH ARE SAME AS ARINC 600-13, DRAFT 2 OF SUPPLIMENT 14 (AIR TRANSPORT AVIONICS EQUIPMENT INTERFACES).

5 TYCO ELECTRONICS LOGO OR TE

OLIVE DRAB	B	1954577-6
OLIVE DRAB	A	1954577-5
OLIVE DRAB	N	1954577-4
NICKEL	B	1954577-3
NICKEL	A	1954577-2
NICKEL	N	1954577-1
SHELL & RETAINER FINISH	SHELL KEYING ARRANGEMENT	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN R FLAIG CHK L OH APVD L OH	20NOV2006 20NOV2006 20NOV2006	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±.01 3 PLC ±.005 4 PLC ±. ANGLES ±1° FINISH		NAME ASSY, RECEPTACLE, SIZE 23, 606, M38999 STYLE, SERIES 111 -	
					
MATERIAL -		WEIGHT -		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-1954577	RESTRICTED TO -
				SCALE 2:1	SHEET 1
				OF 1	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1954577-3](#)