


# INTRODUCING SDE CRIMP

## COMMERCIAL TOOL SYSTEM

We've combined all the features pioneered in our original PRO-CRIMPER hand tools with the versatility of an even more robust design to create the revolutionary SDE Crimp commercial tool system. SDE Crimp minimizes the need for multiple types of hand tools thanks to its Standard Die Envelope (SDE) die sets, which are easily interchangeable from manual to power-assisted tools depending on your needs. An enhanced tool frame also delivers greater operator comfort, efficiency and crimping quality. Available as a fully assembled tool, or with the frame (PN 2362810-1) and die set sold separately, SDE Crimp brings a new level of flexibility and performance to your crimping.



SDE die sets complete the tool's versatility by incorporating a standard locator (shown installed below) or flip locator (shown to the left) for terminal placement and wire brush control. Only available on select models.

Rounded upper jaw design is engineered for increased strength and even distribution of force.

Die sets are easily changed out with a simple screw and pin system

Modular SDE system allows you to quickly change dies from manual to power-assisted hand tools

Ratcheted action frame reduces quality issues associated with under-crimping by not releasing the terminal until the crimp cycle is completed

Bi-material grips deliver better control and ergonomics for repetitive crimping performance

Longer handle design provides greater leverage, reducing the amount of operator force required

Handle force can be adjusted for operator comfort when crimping various terminals



## Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need. Visit [tooling.te.com](https://tooling.te.com) to chat with a product specialist.

---

## Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need. Visit [tooling.te.com](https://tooling.te.com) to chat with a product specialist.

---

### te.com

TE Connectivity, TE Connectivity (logo) and PRO-CRIMPER are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2022 TE Connectivity. All Rights Reserved.

2408317-1 Rev A 2/22

### PRODUCT SHEET

Contact us today to learn more

E-mail (Americas): [toolsales@te.com](mailto:toolsales@te.com)

Phone (Americas): 800-722-1111 or 717-986-3434

Phone (EMEA): +49-6251-133-3936

Phone (APAC): +86 21 3325 9030

Field service: [www.te.com/fieldservice](https://www.te.com/fieldservice)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2379969-1](#)