

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00						
			P	REVISED PER ECO-11-004820	11MAR11	RK	HMR

- NOTES:
- 1

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, BLACK, UL94V-0.
- 2


MACHINED CONTACT: BECU, PLATED WITH 20μ” MIN. GOLD THK. OVER 30-100μ” THK. NICKEL.
- 3

SLEEVE: COPPER, PLATED WITH 180-340μ” THK. TIN (LEAD FREE) OVER 75-125μ” THK. NICKEL.
- 4

PARTS ARE END-TO-END STACKABLE AND BREAKABLE TO CREATE VARIOUS POSITION SIZES.
- 5

PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 6







OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

TOLERANCE ±.002 UNLESS OTHERWISE NOTED

<div>6</div> <div>OBSOLETE</div>	2.000	20	2-1571994-0
	1.900	19	1-1571994-9
	1.800	18	1-1571994-8
	1.700	17	1-1571994-7
	1.600	16	1-1571994-6
	1.500	15	1-1571994-5
	1.400	14	1-1571994-4
	1.300	13	1-1571994-3
	1.200	12	1-1571994-2
<div>6</div> <div>OBSOLETE</div>	1.100	11	1-1571994-1
	1.000	10	1-1571994-0
	0.900	9	-1571994-9-
<div>6</div> <div>OBSOLETE</div>	0.800	8	1571994-8
	0.700	7	-1571994-7-
	0.600	6	-1571994-6-
	0.500	5	-1571994-5-
<div>6</div> <div>OBSOLETE</div>	0.400	4	-1571994-4-
	0.300	3	1571994-3
	0.200	2	1571994-2
<div>6</div> <div>OBSOLETE</div>	0.100	1	-1571994-1-
DIM "A"		POSITION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B S VISVESWARA		26APR05		<div><div></div><div>TE Connectivity</div></div>									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK K.WRIGHT		APVD —		NAME							
		0 PLC ± —		PRODUCT SPEC		—		ASSEMBLY SOCKET (.510 SERIES. S.I.P)							
		1 PLC ± —		—		—									
		2 PLC ± —		—		—									
		3 PLC ± —		APPLICATION SPEC		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		4 PLC ± —		—		—		A2		00779		C=1571994		—	
		ANGLES ± —		—		—		—		—		—		—	
MATERIAL 		FINISH  		WEIGHT —		—		—		—		—		—	
CUSTOMER DRAWING								SCALE 4:1		SHEET 1 of 1		REV P		—	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1571994-0](#)