




NOTES:
1) Standoff length selection per Order Table below
2) U.S. & Foreign Pat. Issued & Pend.

REVISIONS				
ECN #	REV	DESCRIPTION	DATE	INITIALS
	N/A	INITIAL RELEASE	9/01/92	JS
	001	REVISED PER ECR111009AZ01	2/25/10	KH



SECTION A-A



ISOMETRIC VIEW

ODERING CODES: STD XXX BLK

XXX = LENGTH (.100 to 1.0)									
100	200	300	400	500	600	700	800	900	1000
110	210	310	410	510	610	710	810	910	
120	220	320	420	520	620	720	820	920	
130	230	330	430	530	630	730	830	930	
140	240	340	440	540	640	740	840	940	
150	250	350	450	550	650	750	850	950	
160	260	360	460	560	660	760	860	960	
170	270	370	470	570	670	770	870	970	
180	280	380	480	580	680	780	880	980	
190	290	390	490	590	690	790	890	990	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		MATERIAL		VISUAL COMMUNICATIONS COMPANY, INC.			
ANGLES DECIMALS ±.020 XXX ±.010 FINISH XXX ±.005		VALOX 310 SEO (BLACK) U.L. 94 V0		190 Bosstick Boulevard, Suite 101 San Marcos, CA 92069 USA Phone (760) 560-1300 Fax (760) 560-1301 email vccsales@vccite.com			
BEND ALL CORNERS AND SHARP EDGES .031 MAX		FINISH		TITLE:			
		SEE NOTES		STDxxxBLK			
THIRD ANGLE PROJECTION		APPROVAL		SIZE	DWG. NO.	REV	
PROPERTY AND CONFIDENTIAL		DRAWN K.Howard		B	STDxxxBLK_A	001	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF VISUAL COMMUNICATIONS COMPANY, INC. REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN CONSENT OF VISUAL COMMUNICATIONS COMPANY, INC. IS PROHIBITED.		CHECKED DPZ		3/1/10			
		DO NOT SCALE DRAWING		SCALE: 5:1			
				SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[STD 620 BLK](#) [STD140BLK](#) [STD480BLK](#) [STD1000B](#) [STD540BLK](#) [STD900BLK](#) [STD880BLK](#) [STD250BLK](#)
[STD510BLK](#) [STD190BLK](#) [STD320BLK](#) [STD200BLK](#) [STD420BLK](#) [STD800BLK](#) [STD400BLK](#) [STD370BLK](#)
[STD230BLK](#) [STD310BLK](#) [STD570BLK](#) [STD610BLK](#) [STD640BLK](#) [STD660BLK](#) [STD690BLK](#) [STD710BLK](#)
[STD760BLK](#) [STD820BLK](#) [STD860BLK](#) [STD940BLK](#) [STD960BLK](#) [STD980BLK](#) [STD990BLK](#) [STD410BLK](#)
[STD500BLK03](#)