

AX103502 Modular Connectors - FXU FRAME, LC-DUPLEX, 12F, OS2



For more Information
please call

1-800-Belden1



General Description:

FiberExpress Ultra Frame, Single-mode Enhanced (OS2), LC-Duplex, 12-Fiber

Usage (Overall)

Suitable Applications: FiberExpress Ultra Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Related Parts: FiberExpress Ultra Patch Panels Rack Mount and Wall Mount, Splice Trays

Physical Characteristics (Connectivity)

Dimensions

Dimensions:

Height (mm)	Width (mm)	Depth (mm)
38.100	113.284	55.880

Materials

Materials:

Description	Type	Material	Color
Frame		Plastic - UL94V-0	Black
Front Connector Body	LC-DUPLEX	Plastic - UL94V-0	Blue
Adapter Sleeve		Zirconia-Ceramic	

Weight

Weight: 0.113 kg

Included Parts

Included Parts: Dust Caps

Packaging

Packaging: Individually packaged in a plastic bag, Shipped in cardboard box (60/box)

Mechanical Characteristics (Connectivity)

Footprint/Type: 1 inch Pullout

Termination Interface:

Termination	Connection	Durabilities
Front	Mated Connection	500 cycles
Rear	Mated Connection	500 cycles

Connector/Hardware Retention: 50.042 N

Plug/Connector Retention: 50.042 N

Storage Temperature Range: -40°C To +75°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2006

MII Order #39 (China RoHS): EUP 50

AX103502 Modular Connectors - FXU FRAME, LC-DUPLEX, 12F, OS2

Telecommunications Standards: TIA 568.C.3

Suitability

Suitability - Indoor: Yes - Indoor

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For additional information about this product refer to product bulletin NP287, or visit our web site at <http://www.belden.com>.

Product Family

Part Number List:

Description	Multimode OM1 - 62.5um	Multimode OM2 - 50um	Multimode OM3 or OM4 - 50um	Single-Mode OS2	APC	Others
ST-Type 6 fibers	AX103382	-	-	AX103467	-	-
ST-Type 12 fibers	AX103403	-	-	AX103493	-	-
SC Simplex 6 fibers	AX103383	AX103439	AX103453	AX103468	AX103472	-
SC Simplex w/shutter 6 fibers	AX103384	AX103440	AX103454	AX103469	AX103473	-
SC Simplex 12 fibers	AX103404	AX103445	AX103459	AX103494	AX103498	-
SC Duplex 6 fibers	AX103385	AX103441	AX103455	AX103470	AX103474	-
SC Duplex w/shutter 6 fibers	AX103386	AX103442	AX103456	AX103471	AX103475	-
SC Duplex 12 fibers	AX103406	AX103447	AX103461	AX103496	AX103500	-
LC Duplex 6 fibers	AX103387	AX103443	AX103457	AX103476	AX103478	-
LC Duplex w/shutter 6 fibers	AX103388	AX103444	AX103458	AX103477	AX103479	-
LC Duplex 12 fibers	AX103408	AX103449	AX103463	AX103502	AX103504	-
LC Duplex w/shutter 12 fibers	AX103409	AX103450	AX103464	AX103503	AX103505	-
LC Duplex 24 fibers	AX103424	AX103451	AX103465	AX103519	AX103521	-
MT-RJ 6 fibers	AX103389	-	-	AX103859	-	-
MT-RJ 12 fibers	AX103410	-	-	AX103860	-	-
MT-RJ 24 fibers	AX103426	-	-	AX103861	-	-
FC 6 fibers	AX103390	-	-	AX103480	-	-
FC 12 fibers	AX103411	-	-	AX103506	-	-
MPO 6 Adapters	AX103901					
MPO 12 Adapters	AX103902					
Frame w/6 Blanks	-	-	-	-	-	AX103862
Frame Empty	-	-	-	-	-	AX103916

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 0 Revision Date: 03-30-2010

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[AX103502](#)