

AX101870 Faceplates and Panels - MediaFlex Plate, Double gang



For more Information
please call

1-800-Belden1



General Description:

MediaFlex Plate, Double gang

Usage (Overall)

Suitable Applications:	-Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400, 1200, Fiber and Coax.
Related Parts:	Compatible with MediaFlex inserts

Physical Characteristics (Connectivity)

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
4.500	5.180	0.770

Materials

Materials:

Description	Material
Plate	Plastic - UL94V-0

Color

Color:	Almond
---------------	--------

Weight

Weight:	0.100 lbs.
----------------	------------

Included Parts

Included Parts:	windows, paper, 6-32 screws, installation guide
------------------------	---

Packaging

Packaging:	Individually packaged in a suitable plastic bag
-------------------	---

Mechanical Characteristics (Connectivity)

Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
MIL Order #39 (China RoHS):	EUP 50
Safety Listing:	ACA, Bi-national Standard Listed

Suitability

Suitability - Indoor:	Yes
------------------------------	-----

Notes (Overall)

Notes: For proper installation refer to Installation Guide PX102063 included with the product or visit our web site at <http://www.belden.com>

Product Family

Part Numbers:

ddescription	Gray	Almond	Elec. White	Black
MediaFlex Plate Single Gang	AX101745	AX101746	AX101747	AX101748
MediaFlex Plate Double Gang	AX101869	AX101870	AX101871	AX101872

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

AX101870 Faceplates and Panels - MediaFlex Plate, Double gang

AX101870	1 EA	0.333 LB			MEDIAFLEX FACEPLATE DG ALM
----------	------	----------	--	--	----------------------------

Revision Number: 0 Revision Date: 05-31-2009

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[AX101870](#)