

Part Number: AX102677

10GX IDC Block Support



Product Description

10GX IDC Block Support XConnect, 6-port, Black (Empty)

Technical Specifications

Environmental Space:	Indoor
Suitable Applications:	Compatible with Cross-Connect Application or Consolidation Point Application for use with Belden IBDN Systems 10GX, 4800, 2400 and 1200.
Port Count:	6 connectors
Packaging:	Packaged 12 units per bag
Weight:	0.07 g

Materials

Description	Material
Block Support	Lexan

Inductance

Nominal Inductance
0.16 μ H/m
0.16 μ H/ft

Mated Connection

Max. Insertion Loss TIA* (dB)
0.16 dB

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Dimensions (WxHxD)

Width	Height	Depth
6.64	0.97	1.45

Data Category:	N/A
EU Directive Compliance:	EU Directive 2002/95/EC (RoHS)
EU RoHS Compliance Date (yyyy-mm-dd):	2008-12-16
Suitability - Indoor:	Yes
Safety Listing:	UL 1863 and CSA-C22.2

Part Number

Related Parts:	10GX IDC Connecting Block
----------------	---------------------------

Variants

Item #	Color
AX102677	Black

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[AX102677](#)