

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

4		3		2		1																																																																					
ITEM	CONNECTOR PART NO.	DESCRIPTION	IPI CHECK	EOR CHECK	Applicable Tooling																																																																						
1	See Table 1	SR CONNECTOR			BCD																																																																						
2	UL1571, 30 AWG	BLACK			TABLE 1																																																																						
			<table><tr><td>ITEM</td><td>NUMBER OF CIRCUITS</td><td>CONNECTOR PART NO.</td><td>ASSEMBLY PART NUMBER</td><td>TOTAL WIRE REQUIRED</td></tr><tr><td>1</td><td>2</td><td>02SR-3S</td><td>A02SR02SR30K305A</td><td>609.6</td></tr><tr><td>1</td><td>3</td><td>03SR-3S</td><td>A03SR03SR30K305A</td><td>914.4</td></tr><tr><td>1</td><td>4</td><td>04SR-3S</td><td>A04SR04SR30K305A</td><td>1,219.2</td></tr><tr><td>1</td><td>5</td><td>05SR-3S</td><td>A05SR05SR30K305A</td><td>1,524.0</td></tr><tr><td>1</td><td>6</td><td>06SR-3S</td><td>A06SR06SR30K305A</td><td>1,828.8</td></tr><tr><td>1</td><td>7</td><td>07SR-3S</td><td>A07SR07SR30K305A</td><td>2,133.6</td></tr><tr><td>1</td><td>8</td><td>08SR-3S</td><td>A08SR08SR30K305A</td><td>2,438.4</td></tr><tr><td>1</td><td>9</td><td>09SR-3S</td><td>A09SR09SR30K305A</td><td>2,743.2</td></tr><tr><td>1</td><td>10</td><td>10SR-3S</td><td>A10SR10SR30K305A</td><td>3,048.0</td></tr><tr><td>1</td><td>11</td><td>11SR-3S</td><td>A11SR11SR30K305A</td><td>3,352.8</td></tr><tr><td>1</td><td>12</td><td>12SR-3S</td><td>A12SR12SR30K305A</td><td>3,657.6</td></tr><tr><td>1</td><td>13</td><td>13SR-3S</td><td>A13SR13SR30K305A</td><td>3,962.4</td></tr><tr><td>1</td><td>14</td><td>14SR-3S</td><td>A14SR14SR30K305A</td><td>4,267.2</td></tr></table>			ITEM	NUMBER OF CIRCUITS	CONNECTOR PART NO.	ASSEMBLY PART NUMBER	TOTAL WIRE REQUIRED	1	2	02SR-3S	A02SR02SR30K305A	609.6	1	3	03SR-3S	A03SR03SR30K305A	914.4	1	4	04SR-3S	A04SR04SR30K305A	1,219.2	1	5	05SR-3S	A05SR05SR30K305A	1,524.0	1	6	06SR-3S	A06SR06SR30K305A	1,828.8	1	7	07SR-3S	A07SR07SR30K305A	2,133.6	1	8	08SR-3S	A08SR08SR30K305A	2,438.4	1	9	09SR-3S	A09SR09SR30K305A	2,743.2	1	10	10SR-3S	A10SR10SR30K305A	3,048.0	1	11	11SR-3S	A11SR11SR30K305A	3,352.8	1	12	12SR-3S	A12SR12SR30K305A	3,657.6	1	13	13SR-3S	A13SR13SR30K305A	3,962.4	1	14	14SR-3S	A14SR14SR30K305A	4,267.2
ITEM	NUMBER OF CIRCUITS	CONNECTOR PART NO.	ASSEMBLY PART NUMBER	TOTAL WIRE REQUIRED																																																																							
1	2	02SR-3S	A02SR02SR30K305A	609.6																																																																							
1	3	03SR-3S	A03SR03SR30K305A	914.4																																																																							
1	4	04SR-3S	A04SR04SR30K305A	1,219.2																																																																							
1	5	05SR-3S	A05SR05SR30K305A	1,524.0																																																																							
1	6	06SR-3S	A06SR06SR30K305A	1,828.8																																																																							
1	7	07SR-3S	A07SR07SR30K305A	2,133.6																																																																							
1	8	08SR-3S	A08SR08SR30K305A	2,438.4																																																																							
1	9	09SR-3S	A09SR09SR30K305A	2,743.2																																																																							
1	10	10SR-3S	A10SR10SR30K305A	3,048.0																																																																							
1	11	11SR-3S	A11SR11SR30K305A	3,352.8																																																																							
1	12	12SR-3S	A12SR12SR30K305A	3,657.6																																																																							
1	13	13SR-3S	A13SR13SR30K305A	3,962.4																																																																							
1	14	14SR-3S	A14SR14SR30K305A	4,267.2																																																																							
			<table><tr><td colspan="2">Electrical Specifications</td></tr><tr><td colspan="2">Current: 0.7A DC</td></tr><tr><td colspan="2">Voltage: 50V DC</td></tr><tr><td colspan="2"></td></tr><tr><td colspan="2"></td></tr><tr><td colspan="2"></td></tr></table>			Electrical Specifications		Current: 0.7A DC		Voltage: 50V DC																																																																	
Electrical Specifications																																																																											
Current: 0.7A DC																																																																											
Voltage: 50V DC																																																																											
			<table><tr><td>SCALE</td><td colspan="2"></td></tr><tr><td>1: 1</td><td colspan="2"></td></tr><tr><td>DIMENSIONS</td><td colspan="2">All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.</td></tr><tr><td>DRAWN BY</td><td colspan="2">STEVEN PILKINGTON</td></tr><tr><td>CHECKED BY</td><td colspan="2">JUSTIN BAKER</td></tr></table>			SCALE			1: 1			DIMENSIONS	All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.		DRAWN BY	STEVEN PILKINGTON		CHECKED BY	JUSTIN BAKER																																																								
SCALE																																																																											
1: 1																																																																											
DIMENSIONS	All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.																																																																										
DRAWN BY	STEVEN PILKINGTON																																																																										
CHECKED BY	JUSTIN BAKER																																																																										
			<table><tr><td>CUSTOMER NAME</td><td colspan="2">CUSTOMER PART NO.</td></tr><tr><td>DESCRIPTION</td><td colspan="2">1.0 mm Pitch SR Standard Catalog Assembly - 12" Overall Length - Pin out: 1 to 1</td></tr><tr><td>ASSEMBLY PART NO.</td><td colspan="2">SEE TABLE 1</td></tr><tr><td>DRAWING NO. & REVISION</td><td colspan="2">REVISED</td></tr><tr><td>GAM-012</td><td colspan="2">2/25/2016</td></tr></table>			CUSTOMER NAME	CUSTOMER PART NO.		DESCRIPTION	1.0 mm Pitch SR Standard Catalog Assembly - 12" Overall Length - Pin out: 1 to 1		ASSEMBLY PART NO.	SEE TABLE 1		DRAWING NO. & REVISION	REVISED		GAM-012	2/25/2016																																																								
CUSTOMER NAME	CUSTOMER PART NO.																																																																										
DESCRIPTION	1.0 mm Pitch SR Standard Catalog Assembly - 12" Overall Length - Pin out: 1 to 1																																																																										
ASSEMBLY PART NO.	SEE TABLE 1																																																																										
DRAWING NO. & REVISION	REVISED																																																																										
GAM-012	2/25/2016																																																																										
1	Add electrical specifications	6/27/2018	SP																																																																								
REV.	DESCRIPTION	DATE	BY																																																																								
4		3		2		1																																																																					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[A07SR07SR30K305A](#) [A09SR09SR30K305A](#) [A14SR14SR30K203B](#) [A11SR11SR30K203B](#) [A06SR06SR30K305A](#)
[A02SR02SR30K305A](#) [A03SR03SR30K305A](#) [A13SR13SR30K203B](#) [A08SR08SR30K305A](#) [A10SR10SR30K305A](#)
[A12SR12SR30K203B](#) [A04SR04SR30K305A](#)