

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

4		3		2		1																																																																																	
ITEM	CONNECTOR PART NO.	DESCRIPTION	IPI CHECK	EOR CHECK	Applicable Tooling																																																																																		
1	See Table 1	KR CONNECTOR			BCD																																																																																		
2	UL1061, 26 AWG	BLUE			TABLE 1																																																																																		
			<table><tr><td>ITEM</td><td>NUMBER OF CIRCUITS</td><td>CONNECTOR PART NO.</td><td>ASSEMBLY PART NUMBER</td><td>TOTAL WIRE REQUIRED</td></tr><tr><td>1</td><td>2</td><td>02KR-6S-P</td><td>A02KR02KR26E152A</td><td>304.8 mm</td></tr><tr><td>1</td><td>3</td><td>03KR-6S-P</td><td>A03KR03KR26E152A</td><td>457.2 mm</td></tr><tr><td>1</td><td>4</td><td>04KR-6S-P</td><td>A04KR04KR26E152A</td><td>609.6 mm</td></tr><tr><td>1</td><td>5</td><td>05KR-6S-P</td><td>A05KR05KR26E152A</td><td>762 mm</td></tr><tr><td>1</td><td>6</td><td>06KR-6S-P</td><td>A06KR06KR26E152A</td><td>914.4 mm</td></tr><tr><td>1</td><td>7</td><td>07KR-6S-P</td><td>A07KR07KR26E152A</td><td>1,066.8 mm</td></tr><tr><td>1</td><td>8</td><td>08KR-6S-P</td><td>A08KR08KR26E152A</td><td>1,219.2 mm</td></tr><tr><td>1</td><td>9</td><td>09KR-6S-P</td><td>A09KR09KR26E152A</td><td>1,371.6 mm</td></tr><tr><td>1</td><td>10</td><td>10KR-6S-P</td><td>A10KR10KR26E152A</td><td>1,524 mm</td></tr><tr><td>1</td><td>11</td><td>11KR-6S-P</td><td>A11KR11KR26E152A</td><td>1,676.4 mm</td></tr><tr><td>1</td><td>12</td><td>12KR-6S-P</td><td>A12KR12KR26E152A</td><td>1,828.8 mm</td></tr><tr><td>1</td><td>13</td><td>13KR-6S-P</td><td>A13KR13KR26E152A</td><td>1,981.2 mm</td></tr><tr><td>1</td><td>14</td><td>14KR-6S-P</td><td>A14KR14KR26E152A</td><td>2,133.6 mm</td></tr><tr><td>1</td><td>15</td><td>15KR-6S-P</td><td>A15KR15KR26E152A</td><td>2,286 mm</td></tr><tr><td>1</td><td>16</td><td>16KR-6S-P</td><td>A16KR16KR26E152A</td><td>2,438.4 mm</td></tr></table>					ITEM	NUMBER OF CIRCUITS	CONNECTOR PART NO.	ASSEMBLY PART NUMBER	TOTAL WIRE REQUIRED	1	2	02KR-6S-P	A02KR02KR26E152A	304.8 mm	1	3	03KR-6S-P	A03KR03KR26E152A	457.2 mm	1	4	04KR-6S-P	A04KR04KR26E152A	609.6 mm	1	5	05KR-6S-P	A05KR05KR26E152A	762 mm	1	6	06KR-6S-P	A06KR06KR26E152A	914.4 mm	1	7	07KR-6S-P	A07KR07KR26E152A	1,066.8 mm	1	8	08KR-6S-P	A08KR08KR26E152A	1,219.2 mm	1	9	09KR-6S-P	A09KR09KR26E152A	1,371.6 mm	1	10	10KR-6S-P	A10KR10KR26E152A	1,524 mm	1	11	11KR-6S-P	A11KR11KR26E152A	1,676.4 mm	1	12	12KR-6S-P	A12KR12KR26E152A	1,828.8 mm	1	13	13KR-6S-P	A13KR13KR26E152A	1,981.2 mm	1	14	14KR-6S-P	A14KR14KR26E152A	2,133.6 mm	1	15	15KR-6S-P	A15KR15KR26E152A	2,286 mm	1	16	16KR-6S-P	A16KR16KR26E152A	2,438.4 mm
ITEM	NUMBER OF CIRCUITS	CONNECTOR PART NO.	ASSEMBLY PART NUMBER	TOTAL WIRE REQUIRED																																																																																			
1	2	02KR-6S-P	A02KR02KR26E152A	304.8 mm																																																																																			
1	3	03KR-6S-P	A03KR03KR26E152A	457.2 mm																																																																																			
1	4	04KR-6S-P	A04KR04KR26E152A	609.6 mm																																																																																			
1	5	05KR-6S-P	A05KR05KR26E152A	762 mm																																																																																			
1	6	06KR-6S-P	A06KR06KR26E152A	914.4 mm																																																																																			
1	7	07KR-6S-P	A07KR07KR26E152A	1,066.8 mm																																																																																			
1	8	08KR-6S-P	A08KR08KR26E152A	1,219.2 mm																																																																																			
1	9	09KR-6S-P	A09KR09KR26E152A	1,371.6 mm																																																																																			
1	10	10KR-6S-P	A10KR10KR26E152A	1,524 mm																																																																																			
1	11	11KR-6S-P	A11KR11KR26E152A	1,676.4 mm																																																																																			
1	12	12KR-6S-P	A12KR12KR26E152A	1,828.8 mm																																																																																			
1	13	13KR-6S-P	A13KR13KR26E152A	1,981.2 mm																																																																																			
1	14	14KR-6S-P	A14KR14KR26E152A	2,133.6 mm																																																																																			
1	15	15KR-6S-P	A15KR15KR26E152A	2,286 mm																																																																																			
1	16	16KR-6S-P	A16KR16KR26E152A	2,438.4 mm																																																																																			
			<table><tr><td colspan="2">Electrical Specifications</td></tr><tr><td colspan="2">Current: 1.0A AC/DC</td></tr><tr><td colspan="2">Voltage: 100V AC/DC</td></tr><tr><td colspan="2"></td></tr><tr><td colspan="2"></td></tr><tr><td colspan="2"></td></tr></table>			Electrical Specifications		Current: 1.0A AC/DC		Voltage: 100V AC/DC																																																																													
Electrical Specifications																																																																																							
Current: 1.0A AC/DC																																																																																							
Voltage: 100V AC/DC																																																																																							
			<table><tr><td>SCALE</td><td colspan="2"></td></tr><tr><td>1: 1</td><td colspan="2"></td></tr><tr><td>DIMENSIONS</td><td colspan="2">All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.</td></tr><tr><td>DRAWN BY</td><td colspan="2">STEVEN PILKINGTON</td></tr><tr><td>CHECKED BY</td><td colspan="2">JUSTIN BAKER</td></tr></table>			SCALE			1: 1			DIMENSIONS	All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.		DRAWN BY	STEVEN PILKINGTON		CHECKED BY	JUSTIN BAKER																																																																				
SCALE																																																																																							
1: 1																																																																																							
DIMENSIONS	All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.																																																																																						
DRAWN BY	STEVEN PILKINGTON																																																																																						
CHECKED BY	JUSTIN BAKER																																																																																						
			<table><tr><td>CUSTOMER NAME</td><td colspan="2">CUSTOMER PART NO.</td></tr><tr><td>DESCRIPTION</td><td colspan="2">2.0 mm Pitch KR Standard Catalog Assembly - 6" Overall Length - Pin out: 1 to 1</td></tr><tr><td>ASSEMBLY PART NO.</td><td colspan="2">SEE TABLE 1</td></tr><tr><td>DRAWING NO. & REVISION</td><td colspan="2">GAM-023</td></tr><tr><td>REVISED</td><td colspan="2">3/3/2016</td></tr></table>			CUSTOMER NAME	CUSTOMER PART NO.		DESCRIPTION	2.0 mm Pitch KR Standard Catalog Assembly - 6" Overall Length - Pin out: 1 to 1		ASSEMBLY PART NO.	SEE TABLE 1		DRAWING NO. & REVISION	GAM-023		REVISED	3/3/2016																																																																				
CUSTOMER NAME	CUSTOMER PART NO.																																																																																						
DESCRIPTION	2.0 mm Pitch KR Standard Catalog Assembly - 6" Overall Length - Pin out: 1 to 1																																																																																						
ASSEMBLY PART NO.	SEE TABLE 1																																																																																						
DRAWING NO. & REVISION	GAM-023																																																																																						
REVISED	3/3/2016																																																																																						
1			2			3			4																																																																														
REV.			DESCRIPTION			DATE			BY																																																																														
1			Add electrical specifications			6/27/2018			SP																																																																														

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

JST:

[A07KR07KR26E152A](#) [A09KR09KR26E152A](#) [A06KR06KR26E152A](#) [A11KR11DA28W254B](#) [A14KR14DA28W254B](#)
[A13KR13DA28W254B](#) [A03KR03KR26E152A](#) [A08KR08KR26E152A](#) [A05KR05KR26E152A](#) [A15SUR15SUR32W254B](#)
[A15KR15DA28W254B](#) [A12KR12DA28W254B](#) [A02KR02KR26E152A](#) [A10KR10KR26E152A](#) [A04KR04KR26E152A](#)