

4		3		2		1	
ITEM	CONNECTOR PART NO.	DESCRIPTION	IPI CHECK	EOR CHECK	Applicable Tooling		
1	SSHL-002T-P0.2	GH CONNECTOR CONTACT			APPLICATOR		
2	UL1571, 28 AWG	BLACK					

The technical drawing shows a horizontal wire assembly with two end leads. Callout 1 points to the end leads, which are dimensioned as (162 +/- 5.0) mm apart. Callout 2 points to the main body of the wire, which has a length dimension of 152.4 +/- 5.0 mm.

Applicable Housings	
NO. OF CIRCUITS	HOUSING PART NO.
2	GHR-02V-S
3	GHR-03V-S
4	GHR-04V-S
5	GHR-05V-S
6	GHR-06V-S
7	GHR-07V-S
8	GHR-08V-S
9	GHR-09V-S
10	GHR-10V-S
11	GHR-11V-S
12	GHR-12V-S
13	GHR-13V-S
14	GHR-14V-S
15	GHR-15V-S

Electrical Specifications			
Current: 1.0A AC/DC			
Voltage: 50V AC/DC			

SCALE		CUSTOMER NAME	CUSTOMER PART NO.
1: 1			
DIMENSIONS		DESCRIPTION	
All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.		1.25 mm Pitch GH Series Standard Leads - 6" Inside Length DOUBLE-END LEADS	
DRAWN BY		ASSEMBLY PART NO.	
STEVEN PILKINGTON		AGHGH28K152	
CHECKED BY		DRAWING NO. & REVISION	REVISED
JUSTIN BAKER		GAM-047	3/7/2016

REV.	DESCRIPTION	DATE	BY
1	Add electrical specifications	6/27/2018	SP

Electrical Specifications	
Current:	1.0A AC/DC
Voltage:	50V AC/DC

JST

SCALE 1: 1	CUSTOMER NAME	CUSTOMER PART NO.
DIMENSIONS All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.	DESCRIPTION 1.25 mm Pitch GH Series Standard Leads - 6" Inside Length DOUBLE-END LEADS	
DRAWN BY STEVEN PILKINGTON	ASSEMBLY PART NO. AGHGH28K152	
CHECKED BY JUSTIN BAKER	DRAWING NO. & REVISION GAM-047	REVISED 3/7/2016

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[AGHDGHD26K305](#)