

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

1

2

3

4

5

6

7

8

Item No.	Part No.	Description
1	SPHD-001T-P0.5	Contact for PA & PBV
2	UL1061, 22 AWG	Black

Electrical Specifications

Current: 3.0AAC/DC

Voltage: 100V AC/DC

APPLICABLE HOUSINGS					
PA SERIES		PBV SERIES		PHD SERIES	
NO. OF CIRCUITS	HOUSING PART NO.	NO. OF CIRCUITS	HOUSING PART NO.	NO. OF CIRCUITS	HOUSING PART NO.
2	PAP-02V-S	-	-	8	PHDR-08VS
3	PAP-03V-S	3	PBVP-03VS	10	PHDR-10VS
4	PAP-04V-S	4	PBVP-04VS	12	PHDR-12VS
5	PAP-05V-S	-	-	14	PHDR-14VS
6	PAP-06V-S	6	PBVP-06VS	16	PHDR-16VS
7	PAP-07V-S	-	-	18	PHDR-18VS
8	PAP-08V-S	8	PBVP-08VS	20	PHDR-20VS
9	PAP-09V-S	-	-	22	PHDR-22VS
10	PAP-10V-S	10	PBVP-10VS	24	PHDR-24VS
11	PAP-11V-S	-	-	26	PHDR-26VS
12	PAP-12V-S	12	PBVP-12VS	28	PHDR-28VS
13	PAP-13V-S	-	-	30	PHDR-30VS
14	PAP-14V-S	-	-	32	PHDR-32VS
15	PAP-15V-S	15	PBVP-15VS	34	PHDR-34VS
16	PAP-16V-S	-	-	-	-

216.2 +/- 5.0

203.2 +/- 5.0

1

2

1

JST

Drawn By:
Larissa Mosley

Checked By:
Steven Pilkington

Customer Name

Description
2.0mm Pitch PA & PBV & PHD Series Standard Leads - 8" Inside Length
DOUBLE END LEADS, F-F

Size

Customer Part No.

Part No.
APAPA22K203

Rev

Scale
1:1

Drawing No.
GAM-341

Date
5/1/2018

ZONE	REV	DESCRIPTION	DATE	APPROVED
	1	Add Electrical Specifications	7/02/2018	LM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[APAPA22K203](#)