


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

1	2	3	4
Item No.	Part No.	Description	
1	SYM-001T-P0.6	SM Male Connector Contact	
2	SHF-001T-0.8BS	SM Female Connector Contact	
3	UL1007, 22 AWG	Black	

Electrical Specifications
Current: 3A AC/DC
Voltage: 250V AC/DC

APPLICABLE HOUSINGS			
FOR SOCKET CONTACT		FOR PIN CONTACT	
NO. OF CIRCUITS	HOUSING PART NO.	NO. OF CIRCUITS	HOUSING PART NO.
2	SMP-02V-BC	2	SMR-02V-B
	SMP-02V-NC		SMR-02V-N
3	SMP-03V-BC	3	SMR-03V-B
	SMP-03V-NC		SMR-03V-N
4	SMP-04V-BC	4	SMR-04V-B
	SMP-04V-NC		SMR-04V-N
5	SMP-05V-BC	5	SMR-05V-B
	SMP-05V-NC		SMR-05V-N
6	SMP-06V-BC	6	SMR-06V-B
	SMP-06V-NC		SMR-06V-N
7	SMP-07V-BC	7	SMR-07V-B
	SMP-07V-NC		SMR-07V-N
8	SMP-08V-BC	8	SMR-08V-B
	SMP-08V-NC		SMR-08V-N
9	SMP-09V-BC	9	SMR-09V-B
	SMP-09V-NC		SMR-09V-N
10	SMP-10V-BC	10	SMR-10V-B
	SMP-10V-NC		SMR-10V-N
11	SMP-11V-BC	11	SMR-11V-B
	SMP-11V-NC		SMR-11V-N
12	SMP-12V-BC	12	SMR-12V-B
	SMP-12V-NC		SMR-12V-N
18	SMP-18V-BC	18	SMR-18V-B
	SMP-18V-NC		SMR-18V-N



JST

ZONE	REV	DESCRIPTION	DATE	APPROVED
1				
2				
3				
4				

All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.	CUSTOMER NAME			
	DESCRIPTION			
Drawn By: Larissa Mosley Checked By: Steven Pilkington	2.5mm Pitch SM Series Standard Leads - 8" Inside Length DOUBLE END LEADS, M-F			
	SIZE	CUSTOMER PART NO.	PART NO.	REV
	SCALE	1:1	DRAWING NO. GAM-631	DATE 1/8/2019

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[ASMRSMP22K203](#)