

CLI MH 110 HSTR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Version	CableLine, Accessories, 10 - 317 mm, 110 x 11.3 mm, black
Order No.	0189400000
Type	CLI MH 110 HSTR
GTIN (EAN)	4008 190144784
Qty.	100 pc(s).

Creation date January 11, 2022 11:48:59 AM CET

Catalogue status 17.12.2021 / We reserve the right to make technical changes.

CLI MH 110 HSTR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	3 mm	Depth (inches)	0.118 inch
Height	110 mm	Height (inches)	4.331 inch
Width	11.3 mm	Width (inches)	0.445 inch
Net weight	1.29 g		

Temperatures

Operating temperature range	-30...100 °C
-----------------------------	--------------

General data

Colour	black	Material	Polyamide 66
Material colour according to resistance code	0	Number of markers per combination	1 Component part = Accessories
Operating temperature range	-30...100 °C	Operating temperature range, max.	100 °C
Operating temperature range, min.	-30 °C	Recommended industries	Process, Machinery
Type of printing	neutral	UL 94 flammability rating	V-0
Version	halogen-free	Width	11.3 mm

Conductor and cable markers

Conductor O.D.	10 - 317 mm	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 500 mm ²

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

Data sheet

CLI MH 110 HSTR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0189400000](#)