

RKDGE D2X6,5 PT6**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Intelligent cabling solutions can save you valuable time and money.**

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread

Integration of operating and signalling devices into the seal possible

seal possible

General ordering data

Order No.	2443800000
Type	RKDGE D2X6,5 PT6
GTIN (EAN)	4050118457704
Qty.	10 pc(s).

RKDGE D2X6,5 PT6

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.comwww.weidmueller.com**Technical data****Dimensions and weights**

Depth	16 mm	Depth (inches)	0.63 inch
Height	21 mm	Height (inches)	0.827 inch
Width	21 mm	Width (inches)	0.827 inch
Net weight	3.32 g		

Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

General data

Clamping range, max.	6.5 mm ²	Clamping range, min.	4.5 mm ²
Colour	beige	Design	Slotted sealing insert
Line type	round	Material	TPE-V
Mounting position, installation notice	in RKDG D17 PT6 (4324010000)	Protection degree	IP54
UL 94 flammability rating	HB		

Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ECLASS 9.1	27-18-27-90
ECLASS 10.0	27-18-28-15	ECLASS 11.0	27-18-28-15
ECLASS 12.0	27-18-28-15		

Important note

Product information	The foldable seal RKDG D17 PT6 (4324010000) is the carrier seal for the slotted sealing insert. Cables for IP54 with multiple sealing insert 2 x 6.5 mm (2443800000): <ul style="list-style-type: none"> • IE cable Ø 6.5 mm Type: IE-C5DD4UG..... • 24 V cable Ø 6.5 mm E.g. Lapp Ölflex Classic 110 3G1,5
---------------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration FieldPower® Enclosure parts
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2443800000](#)