

**LIR 2,5M8 V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Insulated ring-cable connector made from PVC**

- Commercially available designs
- Not soldered
- With conical entry funnel

**General ordering data**

Version	cable lug, terminal end, Insulated cable connector, 2.5 mm <sup>2</sup> , 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
Order No.	<a href="#">9200200000</a>
Type	LIR 2,5M8 V
GTIN (EAN)	40322484 10026
Qty.	100 pc(s).

Creation date September 18, 2022 4:53:17 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

**LIR 2,5M8 V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	6.2 mm	Depth (inches)	0.244 inch
Width	29.3 mm	Width (inches)	1.154 inch
Net weight	1.002 g		

**Technical data**

Description of article	Insulated ring-cable connector 2.5 mm <sup>2</sup> / M8
------------------------	---

**Connectors**

Conductor cross-section	2.5 mm <sup>2</sup>	Conductor cross-section, max.	2.5 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Connection density (S1)	0.8 mm
Dimension	M 8	Dimension (bolt)	M 8
Identification colour	blue	Inside diameter (d1)	8.4 mm
Insulation	Available	Material/plastic	PVC
Outside diameter (d)	14 mm	Plastic collar diameter (D)	4.5 mm
Plastic collar length (b)	11.3 mm		

**Classifications**

ETIM 6.0	EC001059	ETIM 7.0	EC001059
ETIM 8.0	EC001059	ECLASS 9.0	27-40-02-92
ECLASS 9.1	27-40-02-12	ECLASS 10.0	27-40-02-92
ECLASS 11.0	27-40-02-92	ECLASS 12.0	27-40-02-92

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data	<a href="#">EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9200200000](#)