

## SCT-C 4.6/680

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

Cable ties are characterised by maximum tying force and a long life. Steel cable ties also offer permanent fastening under extreme conditions such as high temperatures or severe chemical effects.

- Fully coated stainless steel cable ties
- Secure ball locking mechanism for a fast and simple installation
- Can be attached manually or using a tool
- These cables ties are recommended for special applications, such as for use with saline spray, extreme temperatures or corrosive surroundings.

### General ordering data

Version	Cable ties, 4.6 x 680 mm, Stainless steel, polyester coated, 445 N
Order No.	<a href="#">1015290000</a>
Type	SCT-C 4.6/680
GTIN (EAN)	4032248724260
Qty.	100 pc(s).

Creation date January 18, 2022 10:24:21 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

**SCT-C 4.6/680****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	0.26 mm	Depth (inches)	0.01 inch
Height	680 mm	Height (inches)	26.772 inch
Width	4.6 mm	Width (inches)	0.181 inch
Net weight	6.38 g		

**Temperatures**

Operating temperature range	-80...150 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	165 °C		

**Installation materials**

Bundle diameter, max.	200 mm	Bundle diameter, min.	20 mm
Cable diameter, max.	200 mm	For re-opening	No
Halogen	No	Material	Stainless steel, polyester coated
Operating temperature range, max.	150 °C	Operating temperature range, min.	-80 °C
Tensile strength	445 N	Tensile strength (Pound-force)	100 lbf
UV-resistant	No		

**Classifications**

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02		

**Approvals**

Approvals



ROHS

Conform

**Downloads**

Engineering Data	<a href="#">EPLAN, WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**


**SCT-C 4.6/680**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1015290000](#)