

**WBC-P-10BK-70****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Battery storage systems are playing an increasingly important role in the field of renewable energies. They usually consist of several individual batteries that need to be quick and easy to replace. The Weidmüller Battery Connector (WBC) makes it possible to connect several individual batteries to an ESS in just a few simple steps – and to disconnect the connections just as quickly if required. For more safety and easy handling, the poles are clearly marked: The positive pole in orange and the negative pole in black.

**General ordering data**

Order No.	<a href="#">2991900000</a>
Type	WBC-P-10BK-70
GTIN (EAN)	4099986868717
Qty.	5 pc(s).

## WBC-P-10BK-70

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	72.5 g
------------	--------

## Temperatures

Continuous operating temp., min.	-40 °C	Continuous operating temp., max.	125 °C
Humidity	≤85% RH		

## General Data

Approvals	UL 4128	Colour	black
Conductor cross-section, max.	70 mm <sup>2</sup>	Contact diameter, male Ø	10 mm
Material	PA 66	Surface finish	silver
Type	Female	Type of connection	Crimp connection

## Technical Data

Operating altitude	≤ 2000 m	Plugging cycles	≥ 100
Protection degree	IP67 plugged	Rated current	250 A
Rated voltage	1,500 V	Shock resistance	V2
Surge voltage category	II	UL 94 flammability rating	V-0
Vibration resistance	30g	Volume resistance	≥ 5000 MΩ

## Classifications

ETIM 7.0	EC001121	ETIM 8.0	EC001121
ETIM 9.0	EC001121	ECLASS 10.0	27-44-03-12
ECLASS 11.0	27-44-03-12	ECLASS 12.0	27-44-03-12
ECLASS 13.0	27-44-03-12	ECLASS 14.0	27-44-03-12

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E529699

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Suitable Tools for WBC Battery Connector</a> <a href="#">Montageanleitung WBC P_10_305A</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>


**Data sheet**

**WBC-P-10BK-70**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2991900000](#)