

**WQL 3 WFF70****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Bolt-type screw terminals, Cross-connector, Number of poles: 3
Order No.	<a href="#">1065500000</a>
Type	WQL 3 WFF70
GTIN (EAN)	4008190174811
Qty.	5 pc(s).

Creation date January 20, 2022 4:54:57 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## WQL 3 WFF70

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	3 mm	Depth (inches)	0.118 inch
Height	89 mm	Height (inches)	3.504 inch
Width	20 mm	Width (inches)	0.787 inch
Net weight	41.61 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	Copper - zinc	Colour	grey
----------	---------------	--------	------

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

## Cross-connector

Number of cross-connected terminals	3	Rated current, 2-pole	192 A
Rated current, multi-pole	232 A	Type	Cross-connector

## Dimensions

Pitch in mm (P)	32 mm
-----------------	-------

## General

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

## Rating data

Rated current	192 A
---------------	-------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40		

## Approvals

Approvals



ROHS	Conform
------	---------

**WQL 3 WFF70**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1065500000](#)