

SAI-M23-KSC-0.08/0.56**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Version	Sensor/Actuator plug-in connector, Crimp contact
Order No.	1170140000
Type	SAI-M23-KSC-0.08/0.56
GTIN (EAN)	4032248962235
Qty.	50 pc(s).

Creation date September 16, 2022 1:35:15 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

SAI-M23-KSC-0.08/0.56

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 0.26 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1 SCIP ebf89fc8-a87f-4691-b87a-dfb9921774b4

Settings re. SAI M23 crimping tool

Settings regarding SAI M23 crimping tool	Locator position	11		
	Crimping Tool	1		
	Crimp contact	Crimp male 1 mm		
	Crimping mandrel adjustment acc. to mm ²	Wire cross-section	0.08 mm ²	
		Crimping mandrel adjustment	0.78	
		Wire cross-section	0.14 mm ²	
		Crimping mandrel adjustment	0.81	
	Locator position	1		
	Crimping Tool	2		
	Crimp contact	Crimp male 1 mm		
	Crimping mandrel adjustment acc. to mm ²	Wire cross-section	0.08 mm ²	
		Crimping mandrel adjustment	0.72	
		Crimping mandrel adjustment	0.72	

Technical data customisable plug-in connectors

Conductor cross-section, max.	0.56 mm ²	Conductor cross-section, min.	0.08 mm ²
Contact surface	Gold-plated	Insulation strength	> 10 ¹⁰ Ω
Plugging cycles	> 1000	Type of connection	Crimp connection

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-02-90	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92

Important note

Product information Enclosures, inserts and crimp contacts need to be ordered separately.

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E344862

Creation date September 16, 2022 1:35:15 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

SAI-M23-KSC-0.08/0.56**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Technical data****Downloads**

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

Data sheet


SAI-M23-KSC-0.08/0.56

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1170140000](#)