

**Q 10 WDL2.5S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****Building installation wiring**

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

**General ordering data**

Version	W-Series, Cross-connector, For the terminals, Number of poles: 10
Order No.	<a href="#">1071800000</a>
Type	Q 10 WDL2.5S
GTIN (EAN)	4008 190424893
Qty.	20 pc(s).

**Q 10 WDL2.5S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	9.5 mm	Depth (inches)	0.374 inch
Height	58.9 mm	Height (inches)	2.319 inch
Width	4 mm	Width (inches)	0.157 inch
Net weight	7.7 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1	SCIP	abe9d042-078a-4094-b143-0a6a4ced35a2
------------	----------------	------	--------------------------------------

**Material data**

Material	tinned copper	Colour	yellow
----------	---------------	--------	--------

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
Type of fixing	when screwed in		

**Dimensions**

Pitch in mm (P)	6.1 mm
-----------------	--------

**General**

Installation advice	Feed-through (bushing), Direct mounting	Number of poles	10
---------------------	--	-----------------	----

**Rating data**

Rated current	24 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**Approvals**

Approvals



ROHS	Conform
------	---------

Creation date September 15, 2022 11:36:55 PM CEST

**Q 10 WDL2.5S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1071800000](#)