

WQV 35N/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

General ordering data

| | |
|------------|---|
| Version | W-Series, Cross-connector, For the terminals, Number of poles: 3 |
| Order No. | 1079300000 |
| Type | WQV 35N/3 |
| GTIN (EAN) | 4008 190378288 |
| Qty. | 20 pc(s). |

Creation date January 20, 2022 8:19:18 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

WQV 35N/3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 20.95 mm | Depth (inches) | 0.825 inch |
| Height | 44.8 mm | Height (inches) | 1.764 inch |
| Width | 9 mm | Width (inches) | 0.354 inch |
| Net weight | 16 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|--------|
| Material | PA 66 | Colour | yellow |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|---------------------|-----------------|----------------|-----------------|
| Installation advice | Direct mounting | Type of fixing | when screwed in |
|---------------------|-----------------|----------------|-----------------|

Cross-connector

| | | | |
|--|--------------|---------------------------|-----------------|
| Number of cross-connected terminals | 3 | Rated current, multi-pole | 125 A |
| Tightening torque range for fixing screw | 1.2...2.4 Nm | Type | Cross-connector |

Dimensions

| | |
|-----------------|-------|
| Pitch in mm (P) | 16 mm |
|-----------------|-------|

General

| | | | |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 3 |
|---------------------|-----------------|-----------------|---|

Rating data

| | |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ECLASS 9.0 | 27-14-11-40 |
| ECLASS 9.1 | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 | | |

Approvals

Approvals



ROHS Conform

Creation date January 20, 2022 8:19:18 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

WQV 35N/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Downloads**

| | |
|---|--|
| Approval/Certificate/Document of Conformity | EAC certificate |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| User Documentation | Beipackzettel_WQV.pdf StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Data sheet**WQV 35N/3**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Cutting and notching tools for cross-connections**

- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

General ordering data

| | | |
|------------|----------------------------|---------------------|
| Type | WAW 1 NEUTRAL | Version |
| Order No. | 9004500000 | Miscellaneous tools |
| GTIN (EAN) | 4008190053925 | |
| Qty. | 1 pc(s). | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1079300000](#)