


SAI-M23-BE-17-10 MM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

| | |
|------------|-----------------------------------|
| Version | Sensor/Actuator plug-in connector |
| Order No. | 1224350000 |
| Type | SAI-M23-BE-17-10 MM |
| GTIN (EAN) | 4050118008234 |
| Qty. | 1 pc(s). |

SAI-M23-BE-17-10 MM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|------|
| Net weight | 13 g |
|------------|------|

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

Technical data customisable plug-in connectors

| | | | |
|-----------------------|--------------------------------------|--------------------|-------------|
| Coding | none | Contact surface | Gold-plated |
| Housing main material | Thermoplastic polyamide PA 6, PBT | Number of poles | 17 |
| Plugging cycles | > 1000 | Pollution severity | 3 |
| Rated current | 8 A | Rated voltage | 160 V |
| Type of connection | Solder connection | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000438 | ETIM 7.0 | EC003557 |
| ETIM 8.0 | EC003557 | ECLASS 9.1 | 27-44-02-05 |
| ECLASS 10.0 | 27-44-02-23 | ECLASS 11.0 | 27-44-02-23 |

Important note

| | |
|---------------------|---|
| Product information | Enclosures, inserts and crimp contacts need to be ordered separately. |
|---------------------|---|

Approvals

Approvals



| | |
|-----------------------|---------|
| ROHS | Conform |
| UL File Number Search | E344862 |

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |


Data sheet

SAI-M23-BE-17-10 MM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1224350000](#)