

SAIBC-WDF-D-RR-6.6-C5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

General ordering data

Version	Panel feed-through, Number of poles: 4, Coding: D, M12, 50 V
Order No.	1380640000
Type	SAIBC-WDF-D-RR-6.6-C5
GTIN (EAN)	4050118182477
Qty.	1 pc(s).

Creation date January 23, 2022 8:48:28 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

SAIBC-WDF-D-RR-6.6-C5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 47 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Technical data customisable plug-in connectors

Cable diameter	6.5 mm, 6.6 mm, 7.3 mm, 8.3 mm	Cable diameter, max.	6.5 mm
Cable glands	M 16	Coding	D
Connection cross-section, max.	0.5 mm ²	Connection cross-section, min.	0.34 mm ²
Contact surface	Gold-plated	Number of poles	4
Plugging cycles	≥ 200	Pollution severity	3
Protection degree	IP67	Rated current	4 A
Rated voltage	50 V	Rated voltage	50 V
Shield connection	Yes	Temperature range of housing	-40 ... +85 °C
Type of connection	Crimp connection		

General technical specifications

Cable glands	M 16	Coding	D
Connection thread	M12	Contact surface	Gold-plated
Number of poles	4	Plugging cycles	≥ 200
Pollution severity	3	Protection degree	IP67
Rated current	4 A	Rated voltage	50 V
Temperature range of housing	-40 ... +85 °C	Type of connection	Crimp connection

Classifications

ETIM 6.0	EC002925	ETIM 7.0	EC002925
ETIM 8.0	EC002925	ECLASS 9.0	27-44-01-06
ECLASS 9.1	27-44-01-06	ECLASS 10.0	27-44-01-06
ECLASS 11.0	27-44-01-06		

Approvals

Approvals



ROHS

Conform

Downloads

Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAIBC-WDF-D-RR-6.6-C5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**...for M12**

Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

General ordering data

Type	SAI-TMCDC	Version
Order No.	1381710000	Pressing tool
GTIN (EAN)	4050118183764	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1380640000](#)