

KSW 2,5 24/3,5 1-24

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

KSW marking strips are used to identify multi-pole PCB plug-in connectors. Users can print them individually without being confined to a certain pitch.

- Smudge-proof labelling
- Strips 2.5 mm and 4 mm wide
- Simply stick on - finished
- Optimum adhesion
- PVC-free

General ordering data

Version	KSW, Terminal marker, 2.5 x 84 mm, Pitch in mm (P): 3.50 Weidmueller, white
Order No.	1652250001
Type	KSW 2,5 24/3,5 1-24
GTIN (EAN)	4008 190402 129
Qty.	10 pc(s).
Alternative product	1629920000

Creation date January 27, 2022 3:01:02 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

KSW 2,5 24/3,5 1-24

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	2.5 mm	Height (inches)	0.098 inch
Width	84 mm	Width (inches)	3.307 inch
Net weight	1.4 g		

Temperatures

Operating temperature range	150 °C
-----------------------------	--------

General data

Adhesive	Acrylate	Application/manufacturer	Weidmueller
Colour	white	Colour of printing	black
Material	Polyester, PVC-free	Material colour according to resistance code	9
Number of markers per combination	1 Label reel = Terminal marker	Number per sheet	20
Operating temperature range	150 °C	Operating temperature range, max.	150 °C
Orientation of print	horizontal	Printed characters	Numbers
Printing	1 - 24	Printing method	Thermal transfer
Version	Self-adhesive	Width	84 mm

Classifications

ETIM 6.0	EC000761	ETIM 7.0	EC000761
ETIM 8.0	EC000761	ECLASS 9.0	27-14-11-37
ECLASS 9.1	27-14-11-37	ECLASS 10.0	27-14-11-37
ECLASS 11.0	27-28-11-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1652250001](#)