

SKMU PG36-K SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|--|
| Version | SKMU PA (plastic locknut), Locknut, PG 36, 8 mm, Polyamid 6 (PA6 - GF30) |
| Order No. | 1719170000 |
| Type | SKMU PG36-K SW |
| GTIN (EAN) | 4008 190352394 |
| Qty. | 10 pc(s). |

Creation date January 27, 2022 8:43:13 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

SKMU PG36-K SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 6.16 g

Temperatures

Operating temperature -40 °C... 100 °C

General information

| | | | |
|-----------------------------------|-------------------------|-----------------------------------|---------|
| AF size 1 | 60 mm | Cable glands | PG |
| External thread | PG 36 | Halogen | No |
| Internal thread | PG 36 | Length of thread | 8 mm |
| Material | Polyamid 6 (PA6 - GF30) | O.D. | 69.3 mm |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Thickness | 8 mm | UL 94 flammability rating | HB |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000940 | ETIM 7.0 | EC000940 |
| ETIM 8.0 | EC000940 | ECLASS 9.0 | 27-14-44-24 |
| ECLASS 9.1 | 27-14-44-24 | ECLASS 10.0 | 27-14-44-24 |
| ECLASS 11.0 | 27-14-44-24 | | |

Approvals

Approvals



ROHS Conform

Downloads

| | |
|------------------|--|
| Engineering Data | EPLAN, WSCAD |
| Catalogues | Catalogues in PDF-format |
| Brochures | |


Data sheet

SKMU PG36-K SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1719170000](#)