

SCT 4.6/838

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Weidmüller Steel Series contains a comprehensive assortment of steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 304,
- patented closure enables easy, secure installation,
- patented rounded edges reduce the risk of injury,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

General ordering data

Version	Cable ties, 4.6 x 838 mm, Stainless steel 1.4301, 445 N
Order No.	1699940000
Type	SCT 4.6/838
GTIN (EAN)	4008 190892388
Qty.	100 pc(s).

Creation date January 27, 2022 6:44:27 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

SCT 4.6/838**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	1.2 mm	Depth (inches)	0.047 inch
Height	838 mm	Height (inches)	32.992 inch
Width	4.6 mm	Width (inches)	0.181 inch
Net weight	8 g		

Temperatures

Operating temperature range	-80...538 °C
-----------------------------	--------------

Installation materials

Cable diameter, max.	254 mm	For re-opening	No
Halogen	No	Material	Stainless steel 1.4301
Operating temperature range, max.	538 °C	Operating temperature range, min.	-80 °C
Tensile strength	445 N	Tensile strength (Pound-force)	100 lbf
UV-resistant	No		

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

Data sheet

SCT 4.6/838

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1699940000](#)