

GWDR PG29-PO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|---|
| Version | GWDR PO (flat gasket - polyethylene), Sealing ring, PG 29, Polyethylene |
| Order No. | 1719500000 |
| Type | GWDR PG29-PO |
| GTIN (EAN) | 4008 190352769 |
| Qty. | 50 pc(s). |

Creation date January 27, 2022 8:58:37 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

GWDR PG29-PO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 0.86 g

Temperatures

Operating temperature -30 °C...90 °C

General information

| | | | |
|-----------------------------------|--------------|-----------------------------------|---------|
| Cable glands | PG | Diameter of sealing ring | 43.5 mm |
| External thread | PG 29 | Inside diameter D2 | 37 mm |
| Material | Polyethylene | O.D. | 43.5 mm |
| Operating temperature range, max. | 90 °C | Operating temperature range, min. | -30 °C |
| Sealing | PE-HD | Thickness | 3 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001181 | ETIM 7.0 | EC001181 |
| ETIM 8.0 | EC001181 | ECLASS 9.0 | 27-43-03-19 |
| ECLASS 9.1 | 27-14-44-90 | ECLASS 10.0 | 27-43-03-19 |
| ECLASS 11.0 | 27-43-03-19 | | |

Approvals

ROHS Conform

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | EPLAN, WSCAD |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Data sheet

GWDR PG29-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1719500000](#)