

CC 15/60 K MC NE SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|---------------------|--|
| Version | ClipCard, Device markers, 15 x 60 mm, silver |
| Order No. | 1877360000 |
| Type | CC 15/60 K MC NE SI |
| GTIN (EAN) | 4032248467990 |
| Qty. | 40 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |
| Alternative product | 1072650000 |

Creation date January 28, 2022 10:37:43 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

CC 15/60 K MC NE SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 1.2 mm | Depth (inches) | 0.047 inch |
| Height | 15 mm | Height (inches) | 0.591 inch |
| Width | 60 mm | Width (inches) | 2.362 inch |
| Net weight | 3.35 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

General data

| | | | |
|-----------------------------------|------------------------------|-----------------------------------|--------------|
| Adhesive | Double-sided adhesive tape | Colour | silver |
| Halogen | No | Material | Polyamide 66 |
| Number of markers per combination | 1 MultiCard = Device markers | Operating temperature range | -40...60 °C |
| Operating temperature range, max. | 60 °C | Operating temperature range, min. | -40 °C |
| Recommended industries | Machinery | UL 94 flammability rating | V-2 |
| Version | Self-adhesive | Width | 60 mm |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | EPLAN, WSCAD |
| Product Change Notification | PCN CableLine_DE PCN CableLine_EN |
| Catalogues | Catalogues in PDF-format |

Data sheet

CC 15/60 K MC NE SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



CC 15/60 K MC NE SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Accessories



General ordering data

| | | |
|------------|----------------------------|--|
| Type | ETO CC 15/60 TRANSPAR. | Version |
| Order No. | 1880840000 | ClipCard, Accessories, 15 x 60 mm, Transparent |
| GTIN (EAN) | 4032248481217 | |
| Qty. | 10 pc(s). | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1877360000](#)