

IE-PS-SCRJ-MM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



FO SC-RJ plug-in connectors according to IEC 61754-24
for wire outer diameters 2.6 to 3 mm

General ordering data

Version	FO connector, Plug SCRJ, multimode, IP20
Order No.	1962940000
Type	IE-PS-SCRJ-MM
GTIN (EAN)	4032248653997
Qty.	10 pc(s).

Creation date January 29, 2022 12:17:06 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

IE-PS-SCRJ-MM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 18.6 g

Temperatures

Operating temperature -40 °C...70 °C

General data

Colour	Miscellaneous	Connection 1	SCRJ
Connection 2	gluing, crimping, polishing	Description of article	Plug SCRJ, multimode
Ferrule material	Zirconia	Fibre type	Multimode
Insertion loss	≤ 0.4 dB	Plugging cycles	1000
Protection degree	IP20	Return loss (attenuation)	≥ 30 dB

General standards

Connector standard IEC 61754-24

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22		

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	GOST Approval
Engineering Data	WSCAD
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN

IE-PS-SCRJ-MM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**SC-RJ**

FO SC-RJ plug-in connectors according to IEC 61754-24
for wire outer diameters 2.6 to 3 mm

SC-RJ**General ordering data**

Type	IE-PB-SCRJ-MM	Version
Order No.	1962890000	SCRJ bracket, Multimode, beige
GTIN (EAN)	4032248645084	
Qty.	10 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1962940000](#)