

**SAI-M23-GS-L-7/12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

**General ordering data**

Version	Sensor/Actuator plug-in connector, Empty enclosure
Order No.	<a href="#">1995800000</a>
Type	SAI-M23-GS-L-7/12
GTIN (EAN)	4032248925667
Qty.	1 pc(s).

Creation date January 29, 2022 6:13:55 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## SAI-M23-GS-L-7/12

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight 98 g

## Environmental Product Compliance

REACH SVHC Lead 7439-92-1

## Technical data customisable plug-in connectors

Cable diameter, max.	12 mm	Cable diameter, min.	7 mm
Housing main material	Copper-zinc alloy	Plugging cycles	> 1000
Pollution severity	3	Protection degree	IP67, IP69K
Shield connection	Yes	Temperature range of housing	-40...+125 °C

## Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC003556
ETIM 8.0	EC003556	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-24	ECLASS 11.0	27-44-02-24

## Important note

Product information Enclosures, inserts and crimp contacts need to be ordered separately.

## Approvals

Approvals



ROHS	Conform
UL File Number Search	E344862

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>


**SAI-M23-GS-L-7/12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Dimensioned drawing**



# Cable connector



F

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1995800000](#)