

**CB 390/4.5 BLACK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

**General ordering data**

Version	Cable ties, 4.5 x 390 mm, Polyamide 66, 220 N
Order No.	<a href="#">7940006059</a>
Type	CB 390/4.5 BLACK
GTIN (EAN)	4032248520367
Qty.	100 pc(s).

Creation date January 30, 2022 7:10:36 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

**CB 390/4.5 BLACK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	1.5 mm	Depth (inches)	0.059 inch
Height	390 mm	Height (inches)	15.354 inch
Width	4.5 mm	Width (inches)	0.177 inch
Net weight	2.64 g		

**Temperatures**

Operating temperature range	-40...85 °C
-----------------------------	-------------

**Installation materials**

Bundle diameter, max.	106 mm	Bundle diameter, min.	3.5 mm
Cable diameter, max.	106 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	Tensile strength (Pound-force)	49 lbf
UL 94 flammability rating	V-2	UV-resistant	No

**Classifications**

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02		

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	E317499

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">DE P1830000160627_002</a>
Engineering Data	<a href="#">EPLAN_WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**CB 390/4.5 BLACK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7940006059](#)