

Specification Sheet

Part Number: T18R9PPM4



Polypropylene cable ties deliver excellent resistance to chemicals and salts.

Inside serrations provide strong grip on cables and wire bundles.

Easy application either manually or with a tensioning tool.

Bent tail ensures a quick and simple installation.

Cable Tie, 4" Long, 8lb Tensile Strength, PP, Natural, 1000/pkg

Article Number 111-01922

Type T18R

Color Natural (NA)

Quantity Per bag

Product Description HellermannTyton's polypropylene cable ties offer added resistance to most chemicals. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Cable Tie, 4" Long, 8lb Tensile Strength, PP, Natural, 1000/pkg

Global Part Name	T18R-PP-NA
Minimum Tensile Strength (Imperial)	8
Minimum Tensile Strength (Metric)	35.6
Length L (Imperial)	3.94
Length L (Metric)	100.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.10
Width W (Metric)	2.5
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	0.75
Bundle Diameter Max (Metric)	19.0
Thickness T (Imperial)	0.039

Thickness T (Metric)	1.0
Cable Tie Head Length (Imperial)	0.19
Cable Tie Head Width (Imperial)	0.18
Height H (Imperial)	0.15
Height H (Metric)	3.7
Material	Polypropylene (PP)
Material Shortcut	PP
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +239°F (-40°C to +115°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000

Package Quantity (Metric) 1000

Customs Number 3926909988

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[T18R9PPM4](#)