

Specification Sheet

Part Number: 156-02613



Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation

Fir tree provides low insertion effort yet demonstrates high extraction resistance

Disc feature prevents rattling in high-vibration applications and protects against debris ingress

2-Piece Cable Tie/Fir Tree Mount, 8.0"L, 0.024 - 0.138" Panel Thickness, PA46, Gray, 5000/ctn

Article Number 156-02613

Type T50RFT6ASET

Color Gray (GY)

Quantity Per carton

Product Description HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold unassembled with the cable tie.

Short Description 2-Piece Cable Tie/Fir Tree Mount, 8.0"L, 0.024 - 0.138" Panel Thickness, PA46, Gray, 5000/ctn

Global Part Name T50RFT6ASET-PA46-GY

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225.0

Length L (Imperial) 8.0

Length L (Metric) 203.2

Fixation Method Fir Tree

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.63

Width W (Metric) 16.0

Bundle Diameter Min (Imperial) 0.08

Bundle Diameter Min (Metric) 2.0

Bundle Diameter Max (Imperial) 1.97

Bundle Diameter Max (Metric) 50.0

Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.14
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	3.5
Mounting Hole Diameter D (Imperial)	0.26
Mounting Hole Diameter D (Metric)	6.6 mm
Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02613](#)