

Specification Sheet

Part Number: 170-03081

Provides easy visual and safety identification of critical wiring components.

Offers high tensile strength while maintaining extreme flexibility.

Expands up to 150% of flat diameter for easy installation.

Does not trap heat and humidity.

Installs quickly and accommodates expansions and varying cable assembly shapes, reducing installation costs.



Braided Sleeving, Expandable, 1.5" Dia, PET, Orange, 200 ft/bulk reel

Article Number

170-03081

Type

BSP1123B

Color

Orange (OG), High Voltage (HV)

Quantity Per

reel

Product Description

Orange PET braided sleeving is an extremely flexible, general purpose option for bundling and protecting wires and cables in abrasive type applications. Its color makes it ideal for systematic color coding of complex wiring installations. Commonly used to shield cable harnesses in battery powered vehicles, such as hybrid cars, golf carts and light trucks.

Short Description	Braided Sleeving, Expandable, 1.5" Dia, PET, Orange, 200 ft/bulk reel
Global Part Name	BSP1123B-PET-OG
Length L (Imperial)	200.0
Length L (Metric)	61.0
Bundle Diameter Min (Imperial)	1.5
Bundle Diameter Min (Metric)	38.1
Bundle Diameter Max (Imperial)	3.5
Bundle Diameter Max (Metric)	88.9
Diameter D (Imperial)	1.50
Diameter D (Metric)	38.1
Nominal Diameter (Imperial)	1.5
Nominal Diameter (Metric)	38.1
Material	Polyester (PET)
Material Shortcut	PET
Flammability	FMVSS 302 UL 94 V-0 FAR 25

Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	60.96
Customs Number	5808100000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03081](#)