

## Specification Sheet

Part Number: 170-03154

Flexible construction that conforms to irregular shapes and contours.

Hook and loop feature wraps over cable bundle allowing future access to cables.

Easy access saves assembly time and allows for easy splicing or insertion of additional wires.

Meets military specifications (Mil-202 approved.)

Cuts easily with a benchmount hot knife.

Resists chemicals and cleaning solvents.



Braided Sleeving, Hook & Loop, Flame Retardant, 0.75" Dia, PET, Black, 100 ft/bulk reel

Article Number 170-03154

Type BSHKLPFR340B

Color Black (BK)

Quantity Per reel

Product Description Flame retardant expandable braided sleeving with hook & loop strip for wrapping around cable assemblies. Color matched hook & loop closure provides an easy on and off installation, as well as convenient access for harness break-outs.

Short Description	Braided Sleeving, Hook & Loop, Flame Retardant, 0.75" Dia, PET, Black, 100 ft/bulk reel
Global Part Name	BSHKLPFR340B-PET-BK
Length L (Imperial)	100.0
Length L (Metric)	30.48
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.54
Bundle Diameter Max (Imperial)	0.75
Bundle Diameter Max (Metric)	19.1
Diameter D (Imperial)	0.75
Diameter D (Metric)	19.1
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	19.1
Wall Thickness WT (Imperial)	0.025
Wall Thickness WT (Metric)	0.635

Material	Polyester (PET)
Material Shortcut	PET
US MIL SPEC	MIL-STD-202
Flammability	UL 224 VW-1
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL MIL-STD 202
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	5808100000

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03154](#)