


Specification Sheet

Part Number: 170-03014



Cuts with scissors without fraying ends enables field installations without need for hot knife.

Expands to 150% of easy installation and reduced assembly time requirements.

Material construction offers excellent abrasion and cut-through protection as well as inertness to common chemicals and fungus.

Braided Sleeving, Expandable, Fray Resistant, 1" Dia, PET, Black, 50 ft/reel

Article Number 170-03014

Type BSPSC100

Color Black (BK)

Quantity Per reel

Product Description A versatile and economical general purpose sleeving that resists fraying when cut with ordinary scissors. For use in automotive, industrial and computer applications where the wires, cables and hoses being covered endure frequent handling. It is suited for situations where access to a hot knife is either impractical or impossible.

Short Description Braided Sleeving, Expandable, Fray Resistant, 1" Dia, PET, Black, 50 ft/reel

Global Part Name BSPSC100-PET-BK

Length L (Imperial) 50.0

Length L (Metric) 15.2

Bundle Diameter Min (Imperial) 0.75

Bundle Diameter Min (Metric) 19.1

Bundle Diameter Max (Imperial) 1.19

Bundle Diameter Max (Metric) 30.2

Diameter D (Imperial) 1.0

Diameter D (Metric) 25.4

Nominal Diameter (Imperial) 1

Nominal Diameter (Metric) 25.4

Material Polyester (PET)

Material Shortcut PET

Flammability UL 94 V-0

Halogen Free Yes

UV Resistant (Yes/No)	No
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	15.24
Customs Number	5808100000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03014](#)