

Specification Sheet

Part Number: 170-03206



Tightly woven fabric bundles and protects cables and hoses from sunlight and abrasion damage; also deflects high pressure hose ruptures.

Nylon material resists gasoline, salt and other chemicals.

Cut to size easily with regular scissors.

Braided Sleeving, Heavy Duty, 2.5" Dia, PA6, Black, 50 ft/reel

Article Number 170-03206

Type BSHDWV

Color Black (BK)

Quantity Per box

Product Description Sleeving made of a tightly woven nylon fabric, slides onto hoses, cables and components to protect them from abrasion and environmental elements, including UV damage. Also protects surrounding surfaces from damage.

Short Description Braided Sleeving, Heavy Duty, 2.5" Dia, PA6, Black, 50 ft/reel

Global Part Name BSHDWV-PA6-BK

Length L (Imperial)	50.0
Length L (Metric)	15.24
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.54
Bundle Diameter Max (Imperial)	2.5
Bundle Diameter Max (Metric)	63.5
Diameter D (Imperial)	2.54
Diameter D (Metric)	64.52
Nominal Diameter (Imperial)	2.5
Nominal Diameter (Metric)	63.5
Wall Thickness WT (Imperial)	.045
Wall Thickness WT (Metric)	1.14
Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Halogen Free	Yes

UV Resistant (Yes/No)	No
Operating Temperature	-49°F to +248°F (-45°C to +120°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	15.24
Customs Number	5806322000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03206](#)