

Specification Sheet

Part Number: 170-03197



A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.

Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.

Cuts with ordinary scissors for fast, easy application.

Braided Wrap, Aluminum Laminated Fiberglass, 4' Long Stick, 1.5" Dia, AL/GF, Silver, 4/box

Article Number 170-03197

Type BSHTTSW112SB

Color Silver (SR)

Quantity Per box

Product Description Aluminum Laminated Fiberglass Wrap sleeving combines the protection of bonded aluminum and fiberglass into a robust solution that deflects radiant heat away from sensitive wires and cables. Wrap-around design allows for fast and easy installation and maintenance. Sold in 4-foot sticks.

Short Description Braided Wrap, Aluminum Laminated Fiberglass, 4' Long Stick, 1.5" Dia, AL/GF, Silver, 4/box

Global Part Name	BSHTTSW112SB-GF-AL-SR
Length L (Imperial)	4.0
Length L (Metric)	1.22
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.54
Bundle Diameter Max (Imperial)	1.45
Bundle Diameter Max (Metric)	36.8
Diameter D (Imperial)	1.5
Diameter D (Metric)	38.1
Nominal Diameter (Imperial)	1.5
Nominal Diameter (Metric)	38.1
Wall Thickness WT (Imperial)	0.042
Wall Thickness WT (Metric)	1.06
Material	Glass fiber with aluminium foil (GF-AL)
Material Shortcut	GF-AL

Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-76°F to +491°F (-60°C to +255°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	4
Package Quantity (Metric)	4
Customs Number	7019905150

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03197](#)