


Specification Sheet

Part Number: 181-42008



Strong fingers prevent unwanted breaking.

Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

Supplied with mounting holes to streamline installation.

Optional covers enhance protection and appearance.

Slotted Wall Wiring Duct, 4" x 2", Non-Adhesive, PVC, Gray, 120ft/Carton

Article Number 181-42008

Type SL4X2

Color Gray (GY)

Quantity Per carton

Product Description Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts.

Short Description Slotted Wall Wiring Duct, 4" x 2", Non-Adhesive, PVC, Gray, 120ft/Carton

Global Part Name SL4X2-PVC-GY

| | |
|----------------------------------|-------------------------|
| Length L (Imperial) | 6.0 |
| Length L (Metric) | 1.83 |
| Fixation Method | Non-Adhesive |
| Width W (Imperial) | 4.0 |
| Width W (Metric) | 101.6 |
| Height H (Imperial) | 2.07 |
| Height H (Metric) | 52.6 |
| Mounting Hole Centers (Imperial) | 4.0 |
| Material | Polyvinylchloride (PVC) |
| Material Shortcut | PVC |
| Halogen Free | No |
| UV Resistant (Yes/No) | No |
| Operating Temperature | +122°F (+50°C) |
| Reach Compliant (Article 33) | No |
| ROHS Compliant | Yes |

| | |
|-----------------------------|--|
| Certification/Specification | EN 50085-1:2005 + A1:2013 EN 50085-2-3_1A CSA UL |
| UL Recognized (US) | Yes |
| Package Quantity (Imperial) | 120.0 |
| Package Quantity (Metric) | 36.58 |
| Customs Number | 3925900000 |

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[181-42008](#)