


Specification Sheet

Part Number: 553-50027

Slide Slit and optional center slits for easy wire insertion.
Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.

A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.



ShrinkTrak Labels, 1-Sided, 1-Slit, .38" (9.52mm), PO-X, Yellow, 500/box

Article Number 553-50027

Type HST9-3YE-S

Color Yellow (YE)

Quantity Per box

Product Description HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.

Short Description ShrinkTrak Labels, 1-Sided, 1-Slit, .38" (9.52mm), PO-X, Yellow, 500/box

Global Part Name HST9-3YE-S-PO-X-YE

Variant Thin-Wall

Width W (Imperial) 0.95

Width W (Metric) 24.13

Thickness T (Imperial) .003

Thickness T (Metric) .0762

Height H (Imperial) 0.597

Height H (Metric) 15.16

Width of Liner (Metric) 76.2

Width of Liner (Imperial) 3.0

Outside Diameter OD (Imperial) 0.375

Outside Diameter OD (Metric) 9.52

Outside Diameter Max (Imperial) 0.375

Outside Diameter Max (Metric) 9.52

Wall Thickness WT (Imperial) 0.031

Wall Thickness WT (Metric) 0.79

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	SAE-AMS-DTL-23053/5 Class 1 and 3 SAE-AS81531 MIL-STD-202G Method 215K
Flammability	UL 224 VW-1
Halogen Free	No
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	SAE - AMS - DTL-23053/5 Class 1 and 3 UL 224 125 °C 600V VW-1 SAE - AS81531
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3917320000
Labels per Column	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[553-50027](#)