

Specification Sheet

Part Number: 558-10004

HellermannTyton inkjet ink dries immediately on these labels to reduce or eliminate smearing.

Polyester material resists a wide range of chemicals and solvents. BS5609 synthetic paper available to meet strict marine and maritime labeling requirements.



Can be printed multiple colors, reducing the typical inventory of labels with colored headers and the frequent need to switch stock.

Inkjet Die Cut Roll, 4" x 6", White, Polyester, 50/roll

Article Number 558-10004

Type HT4x6IJWP

Color White (WH)

Quantity Per roll

Product Description

HellermannTyton inkjet label rolls provide flexible options for creating full-color, chemical-resistant labels of all types. Die-cut labels come with rounded corners, ready to print safety, warning and arc-flash labeling. TagPrint® Pro software allows full-color printing of text and images. Using HellermannTyton inkjet labels saves the time and cost of ordering custom signs online, providing on-demand convenience with no minimums or long lead times.

Short Description Inkjet Die Cut Roll, 4" x 6", White, Polyester, 50/roll

Global Part Name HT4x6IJWP-PET-WH

Width W (Imperial) 4.0

Width W (Metric) 101.6

Thickness T (Imperial) .007

Thickness T (Metric) 64.0

Height H (Imperial) 6.0

Height H (Metric) 152.4

Width of Liner (Metric) 101.6

Width of Liner (Imperial) 4.0

Material Polyester (PET)

Material Shortcut PET

Adhesive Acrylic

Halogen Free Yes

UV Resistant (Yes/No) No

Adhesive Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Reach Compliant (Article 33)	Yes
Certification/Specification	CAGE Code 53421
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[558-10004](#)