

## Specification Sheet

Part Number: TAG27-600

Metalized dot matrix polyester has a matte finish, allowing for the highest resolution and print contrast using impact printers.

The acrylic-based adhesive bonds to a wide variety of substrates and can withstand high temperatures long term.

Tabtag dot matrix labels are specifically made for use in dot matrix printers for fast and easy printing.

Labels come with a pin-feed margin to ensure they can easily be loaded into any dot matrix printing system.



Dot Matrix Label, 1.5" x .75", 4 Across, Metalized Polyester, Silver, 5000/pkg

**Article Number** 595-27600

**Type** TAG27

**Color** Silver (SR)

**Quantity Per** pack

**Product Description** HellermannTyton's metalized polyester labels include a layer of metallic particles that give the appearance of being made of metal. Applications include asset tracking and product rating plates. The high operating temperature makes them suitable for use on electronic equipment. Great for replacing expensive metal stampings, engravings and even silk screened rating plates and can be placed on a wide variety of surfaces.

<b>Short Description</b>	Dot Matrix Label, 1.5" x .75", 4 Across, Metalized Polyester, Silver, 5000/pkg
<b>Global Part Name</b>	TAG27-600-SR
<b>Width W (Imperial)</b>	0.75
<b>Width W (Metric)</b>	19.05
<b>Thickness T (Metric)</b>	25.0
<b>Height H (Imperial)</b>	1.5
<b>Height H (Metric)</b>	38.1
<b>Width of Liner (Metric)</b>	193.70
<b>Width of Liner (Imperial)</b>	7.625
<b>Material</b>	Type 600, Polyester, silver-matt (600)
<b>Material Shortcut</b>	600
<b>Adhesive</b>	Acrylic
<b>Halogen Free</b>	No
<b>Adhesive Operating Temperature</b>	-40°F to +302°F (-40°C to +150°C)

<b>Operating Temperature</b>	-40°F to +302°F (-40°C to +150°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	UL-Recognized
<b>UL Recognized (US)</b>	Yes
<b>Package Quantity (Imperial)</b>	5000
<b>Package Quantity (Metric)</b>	5000
<b>Customs Number</b>	3919905060
<b>Labels per Column</b>	4
<b>Labels per Row</b>	4

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TAG27-600](#)