


Specification Sheet

Part Number: 553-50012

Slide Slit and optional center slits for easy wire insertion.
Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.

A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.



ShrinkTrak Labels, 1-Sided, Unslit, .187" (4.74mm), PO-X, Yellow, 250/box

Article Number	553-50012
Type	HST4.8-1.6YE
Color	Yellow (YE)
Quantity Per	box
Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
Short Description	ShrinkTrak Labels, 1-Sided, Unslit, .187" (4.74mm), PO-X, Yellow, 250/box

Global Part Name HST4.8-1.6YE-PO-X-YE

Variant Thin-Wall

Width W (Imperial) 1.9

Width W (Metric) 48.26

Thickness T (Imperial) .003

Thickness T (Metric) .0762

Height H (Imperial) 0.312

Height H (Metric) 7.92

Width of Liner (Metric) 76.2

Width of Liner (Imperial) 3.0

Outside Diameter OD (Imperial) 0.187

Outside Diameter OD (Metric) 4.74

Outside Diameter Max (Imperial) 0.187

Outside Diameter Max (Metric) 4.74

Wall Thickness WT (Imperial) 0.026

Wall Thickness WT (Metric) 0.66

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	SAE-AS81531 MIL-STD-202G Method 215K SAE-AMS-DTL-23053/5 Class 1 and 3
Flammability	UL 224 VW-1
Halogen Free	No
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	SAE - AS81531 UL 224 125 °C 600V VW-1 SAE - AMS - DTL-23053/5 Class 1 and 3
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3917320000
Labels per Column	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[553-50012](#)