

Specification Sheet

Part Number: 596-12203



Convenient tab is easier to remove from the liner, speeding labeling operations.

Tab acts as a guide during positioning or repositioning to ensure a straight wrap and a high-quality appearance.

Tab helps prevent label slippage when applied to cable insulation, reducing labor.

In tests, TabTags increased the average number of wraps per hour by 12 percent, saving time and increasing output.

Thermal Transfer Tab Label, Self-Laminating, 0.5 x 0.37 x 0.82", Vinyl, White, 10M/RL

Article Number 596-12203

Type TAG26T6ES

Color White (WH)

Quantity Per reel

Product Description

HellermannTyton TabTag thermal transfer self-laminating labels are a conformable vinyl film with a white printable surface followed by a clear tail that laminates the printed text when applied to a wire or cable. Handling the label by the tab helps keep fingers off the clear overlay, ensuring years of performance. The labels are UL recognized for indoor use with an aggressive acrylic adhesive that enables the label to bond to large and small diameter wires.

Short Description	Thermal Transfer Tab Label, Self-Laminating, 0.5 x 0.37 x 0.82", Vinyl, White, 10M/RL
Global Part Name	TAG26T6ES-100B-WH
Width W (Imperial)	0.5
Width W (Metric)	12.70
Bundle Diameter Min (Imperial)	0.10
Bundle Diameter Min (Metric)	2.54
Bundle Diameter Max (Imperial)	0.17
Bundle Diameter Max (Metric)	4.32
Height H (Imperial)	0.37
Height H (Metric)	9.39
Width of Liner (Metric)	101.6
Width of Liner (Imperial)	4.00
Material	Type 100B, Vinyl, white transparent, self-laminating (100B)
Material Shortcut	100B

Adhesive	Acrylic
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Adhesive Operating Temperature	-40°F to +205°F (-40°C to +96°C)
Operating Temperature	-40°F to +205°F (-40°C to +96°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	10000
Package Quantity (Metric)	10000
Customs Number	3919102055
Labels per Row	6

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global

customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin.
(www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-12203](#)