






Zener Diodes

(Continued)

POWER	5.0 WATT		10 WATT	50 WATT	
CASE					
ZENER VOLTAGE	INDUSTRY STANDARD	RECOMMENDED FOR NEW DESIGNS	GENERAL PURPOSE	GENERAL PURPOSE	GENERAL PURPOSE
3.6	1N5334B*	CZ5334B			
3.9	1N5335B*	CZ5335B			
4.3	1N5336B*	CZ5336B			
4.7	1N5337B*	CZ5337B			
5.1	1N5338B*	CZ5338B			
5.6	1N5339B*	CZ5339B			
6.0	1N5340B*	CZ5340B			
6.2	1N5341B*	CZ5341B			
6.8	1N5342B*	CZ5342B			1N3305B
7.5	1N5343B*	CZ5343B			1N3306B
8.2	1N5344B*	CZ5344B			1N3307B
8.7	1N5345B*	CZ5345B			
9.1	1N5346B*	CZ5346B			1N3308B
10	1N5347B*	CZ5347B	1N2974B	1N2808B	1N3309B
11	1N5348B*	CZ5348B	1N2975B	1N2809B	1N3310B
12	1N5349B*	CZ5349B	1N2976B	1N2810B	1N3311B
13	1N5350B*	CZ5350B	1N2977B	1N2811B	1N3312B
14	1N5351B*	CZ5351B	1N2978B	1N2812B	1N3313B
15	1N5352B*	CZ5352B	1N2979B	1N2813B	1N3314B
16	1N5353B*	CZ5353B	1N2980B	1N2814B	1N3315B
17	1N5354B*	CZ5354B	1N2981B	1N2815B	1N3316B
18	1N5355B*	CZ5355B	1N2982B	1N2816B	1N3317B
19	1N5356B*	CZ5356B	1N2983B	1N2817B	1N3318B
20	1N5357B*	CZ5357B	1N2984B	1N2818B	1N3319B
22	1N5358B*	CZ5358B	1N2985B	1N2819B	1N3320B
24	1N5359B*	CZ5359B	1N2986B	1N2820B	1N3321B
25	1N5360B*	CZ5360B	1N2987B	1N2821B	1N3322B
27	1N5361B*	CZ5361B	1N2988B	1N2822B	1N3323B
28	1N5362B*	CZ5362B			

For complete specifications, please consult factory.
 ** Reverse polarity available. Simply change "B" suffix to "RB".

* Not recommended for new designs.

See mechanical specifications on page 208

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Central Semiconductor:](#)

[1N2813B](#) [1N2818B](#)