

1-Port European-Style Insert, Coax Coupler (F/F), 22.5 x 45 mm, White, TAA

MODEL NUMBER: N042E-WHM-C1



European-style module accepts a compatible coaxial cable for terminating premise audio/video, voice or data applications.

Features

European Module Connects Your Coaxial Audio/Video, Voice or Data Network

This European-style insert with coax cable connector (F/F) is ideal for your premise wiring applications, including home theater, telephones or radio communications. The insert is compatible with N042E-WF1 wall plate.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white module measures 22.5 x 45 millimeters and blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

Highlights

- Ideal for home theater or VoIP phone in-wall wiring installations
- High-impact plastic construction designed to blend in with your home/office décor
- White insert measures 22.5 x 45 mm for a sleek, professional appearance

Package Includes

N042E-WHM-C1 1-Port Europe-Style Insert, White

Specifications

OVERVIEW	
UPC Code	037332268938
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB 2.0 (High Speed)
Country/Region	Europe
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	KEYSTONE JACK CUTOUT
PHYSICAL	
Color	White
Material of Construction	Brass



Powering Business Worldwide

TRIPP LITE
SERIES

Total Number of Ports	1
Unit Dimensions (hwd / in.)	1.772 x 0.886 x 0.335
Finish	Matte
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N042E-WHM-C1](#)