

## HDMI over Dual Cat5/6 Extender Kit, Wallplate Transmitter/Receiver, Video and Audio, 1920x1200 1080p/60p, Up to 125-ft., TAA

MODEL NUMBER: **B125-101-60-WP**



Transmit a HDMI signal up to 125ft, 1080p @ 60Hz using two Cat6 patch cables

### Description

Tripp Lite's HDMI Over Dual Cat5 Extender Wallplate Kit is the perfect solution for those who need to extend a HDMI signal over a long distance over two Cat5/6 cables.

- When using 24Awg, Solid Wire Cat6 cable, a 1080p @ 60Hz (or 1920 x 1200) signal can be extended up to 125 ft. from the source.
- When using 24Awg, Solid Wire Cat6 cable, a 3D signal can be extended up to 100 ft.
- When using 24Awg, Solid Wire Cat5 cable, a 1080p @ 60Hz (or 1920 x 1200) signal can be extended up to 75 ft. from the source.
- When using 24Awg, Solid Wire Cat5 cable, a 3D signal can be extended up to 50 ft.

Simply run two Cat5/6 cables between the local transmitter and remote receiver units, and plug in standard Tripp Lite HDMI cables to the HDMI source and the display.

The B125-101-60-WP comes with both local transmitter and remote receiver wallplates. DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio are supported, and it is compliant with HDCP, EDID and DDC. 24-bit True Color (8-bits per channel) is supported. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

- Extends a 1080p @ 60Hz (or 1920 x 1200) signal up to 125 ft. using 24Awg, Solid Wire Cat6 cabling (Tripp Lite N202-Series)
- Extends a 1080p @ 60Hz (or 1920 x 1200) signal up to 75 ft. using 24Awg, Solid Wire Cat5 cabling
- Extends a 3D signal up to 100 ft. using 24Awg, Solid Wire Cat6 cabling, or up to 50 ft. using 24Awg, Solid Wire Cat5 cabling
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Supports HDCP, EDID and DDC

### Highlights

- Extends a 1080p @ 60Hz (or 1920 x 1200) signal up to 125 ft. using 24Awg, Solid Wire Cat6\* cabling (Tripp Lite N202-Series)
- Extends a 3D signal up to 100 ft. using 24Awg, Solid Wire Cat6\* cabling (Tripp Lite N202-Series)
- Supports 24-bit True Color (8-bits per channel)
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Supports HDCP, EDID and DDC
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- Local Transmitter and Receiver Units
- External Power Supply with NEMA 1-15P Plug( Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A )
- Screwdriver for Equalization adjustment
- Wallplate screws
- Owners Manual



Powering Business Worldwide



- Supports 24-bit True Color (8-bits per channel)
- Use Tripp Lite P568-Series HDMI cables to connect to HDMI source and monitor
- Equalization control dial for skew compensation
- Supports Lip-Sync Pass Through, and CEC pass through
- Green LED indicate power being received
- Orange LED indicates signal connection
- Compliant with the Federal Trade Agreements Act ( TAA ) for GSA schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332168030
Product Type	Cat5/Cat6 Extender Kit
Technology	HDMI
VIDEO	
Max 720P Range (ft)	125
Max 1080P Range (ft)	125
Maximum Signal Range (ft)	125
Maximum Signal Range (m)	38
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	HDMI (FEMALE)
Side A - Connector 2	(2) RJ45 (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	(2) RJ45 (FEMALE)
PHYSICAL	
Color	White
Shipping Dimensions (hwd / in.)	2.00 x 6.30 x 8.40
Shipping Dimensions (hwd / cm)	5.08 x 16.00 x 21.34
Shipping Weight (lbs.)	1.20
Shipping Weight (kg)	0.54
COMMUNICATIONS	

Max 1024 x 768 Range (ft)	125
Max 480P Range (ft)	125
Max 1440 x 900 Range (ft)	125
Max 1080i Range (ft)	125
Max 480i Range (ft)	125
Max 640 x 480 Range (ft)	125
Max 800 x 600 Range (ft)	125
Max 1600 x 1200 Range (ft)	125
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B125-101-60-WP](#)