

## 2U UPS Replacement 48VDC Battery Cartridge for Select SmartPro UPS

MODEL NUMBER: RBC49-DV



### Highlights

- Certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leakproof construction
- Maintenance free
- Wide operating temperature range

### Package Includes

- One pre-assembled battery pack consisting of four 12V batteries

### Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications and ships ready for installation. Reusable packaging holds expired batteries for recycling center delivery. See the UPS replacement battery web page to confirm compatibility and quantity required.

COMPATIBLE WITH SM2200RMDVTAA ONLY

### Features

- Restores UPS runtime performance to original specifications
- Comes pre-assembled and ready for installation
- Reusable packaging holds expired batteries for recycling center delivery

## Specifications

| OVERVIEW                         |   |
|----------------------------------|---|
| UPC Code                         | 037332155672  |
| BATTERY                          |   |
| DC System Voltage (VDC)          | 48  |
| Included Battery Set             | Contains (4) 12V 9AH sealed lead acid batteries     |
| Typical Battery Lifespan         | 3 to 5 years, depending on UPS operating conditions |
| PHYSICAL                         |   |
| Rack Height                      | 2U  |
| Minimum Required Rack Depth (cm) | 25.40   |



Powering Business Worldwide



|   |                            |
|---|----------------------------|
| Minimum Required Rack Depth (inches)    | 10                         |
| Shipping Dimensions (hwd / in.)         | 9.25 x 15.00 x 11.25       |
| Shipping Dimensions (hwd / cm)          | 23.50 x 38.10 x 28.58      |
| Shipping Weight (lbs.)                  | 31.25                      |
| Shipping Weight (kg)                    | 14.17                      |
| Unit Dimensions (hwd / in.)             | 4.500 x 10.250 x 6.250     |
| Unit Dimensions (hwd / cm)              | 11.4 x 26 x 15.9           |
| Unit Weight (lbs.)                      | 29.5                       |
| Unit Weight (kg)                        | 13.38                      |
| <b>ENVIRONMENTAL</b>                    |                            |
| Relative Humidity                       | 0-95% non-condensing       |
| <b>STANDARDS &amp; COMPLIANCE</b>       |                            |
| Product Compliance                      | Trade Agreements Act (TAA) |
| <b>WARRANTY &amp; SUPPORT</b>           |                            |
| Product Warranty Period (U.S. & Canada) | 18-month limited warranty  |
| Product Warranty Period (International) | 1-year limited warranty    |
| Product Warranty Period (Mexico)        | 1-year limited warranty    |
| Product Warranty Period (Puerto Rico)   | 1-year limited warranty    |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[RBC49-DV](#)