

FC to LC 62.5/125 Adapter for Multi-Function Optical Fiber Cable Tester (M/F)

MODEL NUMBER: **T020-001-LC62**



Converts FC connector on Tripp Lite Multi-Function Optical Fiber Cable Tester to an LC connector. Ideal for cable installers or anyone else working in telecom or LAN environments.

Description

The T020-001-LC62 FC to LC 10 Gb Adapter converts a native FC fiber female port on the T020-001-PSF Multi-Function Optical Fiber Cable Tester to an LC female port for 62.5/125 multimode cable testing. "62.5/125" is clearly labeled on the unit to differentiate the T020-001-LC62 from other adapters. Included dust caps keep the connectors clean when not in use.

Features

Converts Cable Tester's FC Connector to an LC Connector

- Ideal for cable installers or anyone else working in telecom or LAN environments
- Perfect for 62.5/125 multimode cable testing
- FC male plug connects to cable tester's FC female jack
- Included dust caps keep connectors clean
- For use with T020-001-PSF Multi-Function Optical Fiber Cable Tester

Specifications

| OVERVIEW | |
|-------------------------|---------------|
| UPC Code | 037332197658 |
| Technology | Multimode |
| PHYSICAL | |
| Color | Beige; Silver |
| Clad Diameter (microns) | 125 |
| Core Diameter (microns) | 62.5 |

Highlights

- Converts native FC jack to an LC female connector
- FC male plug connects to fiber cable tester's FC female jack
- Perfect for 62.5/125 multimode cable testing
- Included dust caps keep connectors clean
- For use with T020-001-PSF Optical Fiber Cable Tester

System Requirements

- T020-001-PSF Multi-Function Optical Fiber Cable Tester

Package Includes

- T020-001-LC62 FC to LC 62.5/125 Adapter

| | |
|-------------------------------------|---------------------------|
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.04 |
| Shipping Weight (kg) | 0.02 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[T020-001-LC62](#)